

**CC 30/60 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | ClipCard, Device markers, 30 x 60 mm, Holder CC-H 30/60, white                   |
| Order No.          | <a href="#">1934420000</a>   |
| Type               | CC 30/60 MC NE WS  |
| GTIN (EAN)         | 4032248590964  |
| Qty.               | 30 pc(s).  |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## CC 30/60 MC NE WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 1.2 mm | Depth (inches)  | 0.047 inch |
| Height     | 30 mm  | Height (inches) | 1.181 inch |
| Width      | 60 mm  | Width (inches)  | 2.362 inch |
| Net weight | 4.6 g  |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## General data

|  |                              |           |  |
|--|------------------------------|-----------|--|
| Application/manufacture                      | Holder CC-H 30/60            |           |  |
| Colour                                       | white                        |           |  |
| Halogen                                      | No                           |           |  |
| Material                                     | Polyamide 66                 |           |  |
| Material colour according to resistance code | 9                            |           |  |
| Number of markers per combination            | 1 MultiCard = Device markers |           |  |
| Number of markers per packaging unit         | Form of supply               | MultiCard |  |
| Operating temperature range                  | -40...100 °C                 |           |  |
| Operating temperature range, max.            | 100 °C                       |           |  |
| Operating temperature range, min.            | -40 °C                       |           |  |
| Recommended industries                       | Machinery                    |           |  |
| UL 94 flammability rating                    | V-2                          |           |  |
| Width  | 60 mm                        |           |  |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification | <a href="#">Technical change to MultiCard material - DE</a><br><a href="#">Technical change to MultiCard material - EN</a><br><a href="#">MultiCard Material modification</a><br><a href="#">MultiCard Material Modifikation</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |

**CC 30/60 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**CC 30/60 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories****General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | STR CC 30/60 TRANSPARENT   | Version  |
| Order No.  | <a href="#">1934450000</a> | ClipCard, Accessories, 30 x 60 mm, Transparent |
| GTIN (EAN) | 4032248590988              |  |
| Qty.       | 10 pc(s).                  |  |
| Type       | CC-H 30/60                 | Version  |
| Order No.  | <a href="#">1934430000</a> | ClipCard, Accessories, 30 x 60 mm, black       |
| GTIN (EAN) | 4032248590995              |  |
| Qty.       | 10 pc(s).                  |  |
| Type       | ETO CC 30/60 TRANSPAR.     | Version  |
| Order No.  | <a href="#">1934440000</a> | ClipCard, Accessories, 30 x 60 mm, Transparent |
| GTIN (EAN) | 4032248590971              |  |
| Qty.       | 10 pc(s).                  |  |