

SAI-SCREWTY TOOL BOX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**The ideal tool for any application**

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Version	Bolting tool
Order No.	1939170000
Type	SAI-SCREWTY TOOL BOX
GTIN (EAN)	4032248615490
Qty.	1 pc(s).
Packaging	Plastic case + form insert

SAI-SCREWTY TOOL BOX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	1,320 g
------------	---------

Screwing tools

Torque setting, max.	7 Nm	Torque setting, min.	0.5 Nm
----------------------	------	----------------------	--------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Important note

Product information	<p>Included in delivery:</p> <ul style="list-style-type: none"> • Torque screwdriver 0.5-1.7 Nm + Setting aid • Torque screwdriver 2.0-7.0 Nm • Interchangeable blade 1/4 inch • Attachment M8 for moulded lines • Attachment M8F for customisable connectors • Attachment M12 for moulded lines • Attachment M12F for customisable connectors • Blade set: <ul style="list-style-type: none"> Torx T8 / T10 / T20 / T25 Allen key 2.5 / 3.0 / 4.0 Crosshead PH0 / PH1 / PH2 Slotted 0.5x3.0 / 0.6x3.5 / 0.8x4.0 • Plastic Case + Form insert
---------------------	---

Downloads

Product Change Notification	20210319 Technical change to Screwty® torque screwdriver 20210319 Technische Änderung zu Screwty® Drehmomentschraubendreher
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN