

**DMS PRO ZERT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Only for Europe



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Version	Mounting tool
Order No.	<a href="#">1987840000</a>
Type	DMS PRO ZERT
GTIN (EAN)	4050118372359
Qty.	1 pc(s).

**DMS PRO ZERT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Width	276 mm	Width (inches)	10.866 inch
Net weight	480 g		

**Technical data**

Description of article	Mains-operated torque screwdriver with 1/4" drive
------------------------	---

**Electric screwdriver**

Rechargeable batteries	Li-Ion battery	Torque setting, max.	3 Nm
Torque setting, min.	0.36 Nm	Weight	500 g

**Screwing tools**

Torque setting, max.	3 Nm	Torque setting, min.	0.36 Nm
----------------------	------	----------------------	---------

**Classifications**

ETIM 6.0	EC001395	ETIM 7.0	EC001395
ETIM 8.0	EC001395	ETIM 9.0	EC001395
ECLASS 9.0	21-05-21-90	ECLASS 9.1	21-04-04-17
ECLASS 10.0	21-05-21-90	ECLASS 11.0	21-05-08-90
ECLASS 12.0	21-05-08-90	ECLASS 13.0	21-05-08-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">1987840000_DECLARATION_OF_CONFORMITY.pdf</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## DMS PRO ZERT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings


### Example of use



### Example of use



### Example of use



## DMS PRO ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 1,0X5,5X70	Version
Order No.	<a href="#">9024040000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852665	
Qty.	5 pc(s).	
Type	BIT E6,3 0,5X3,0X70	Version
Order No.	<a href="#">9024000000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852634	
Qty.	5 pc(s).	
Type	BIT E6,3 0,8X4,0X70	Version
Order No.	<a href="#">9024030000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852658	
Qty.	5 pc(s).	
Type	BIT E6,3 0,6X3,5X70	Version
Order No.	<a href="#">9024020000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852627	
Qty.	5 pc(s).	
Type	BIT E6,3 Z 0,8X4,0X39	Version
Order No.	<a href="#">9025590000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190151935	
Qty.	10 pc(s).	
Type	BIT E6,3 0,4X2,5X70	Version
Order No.	<a href="#">9202750000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504725	
Qty.	5 pc(s).	
Type	BIT E6,3 1,2X6,5X70	Version
Order No.	<a href="#">9202740000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504718	
Qty.	5 pc(s).	

## DMS PRO ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	AKKU DMS PRO	Version
Order No.	<a href="#">1479110000</a>	Mounting tool
GTIN (EAN)	4050118348712	
Qty.	1 pc(s).	
Type	DMS PRO SET	Version
Order No.	<a href="#">1479090000</a>	Mounting tool
GTIN (EAN)	4050118286786	
Qty.	1 pc(s).	

## E6.3 bits - Phillips / recess

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits are Phillips-Recessed type PH/DIN 5260.  
1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 PH2X70	Version
Order No.	<a href="#">9024090000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870720	
Qty.	5 pc(s).	
Type	BIT E6,3 PH1X70	Version
Order No.	<a href="#">9024080000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870744	
Qty.	5 pc(s).	

## DMS PRO ZERT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## E6.3 bits - Pozidriv / Supadriv



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3 DIN 3126

## General ordering data

Type	BIT E6,3 PZ1X70	Version
Order No.	<a href="#">9024100000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870713	
Qty.	5 pc(s).	
Type	BIT E6,3 PZ2X70	Version
Order No.	<a href="#">9024110000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870706	
Qty.	5 pc(s).	

## Bit assortment, E6.3



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

## General ordering data

Type	BIT-BOX WI DMS 3	Version
Order No.	<a href="#">9024970000</a>	Accessories, Mounting tool
GTIN (EAN)	4032248068067	
Qty.	1 pc(s).	

**DMS PRO ZERT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****DMS 3**

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Type	LG DMS PRO/ DMS 3	Version
Order No.	<a href="#">9007460000</a>	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
GTIN (EAN)	4008190404970	
Qty.	1 pc(s).	