

IE-PH-AD-V05M-RJ45**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC plug-in connector according to IEC 61076-3-106
ver.5 in metal, empty housing

General ordering data

| | |
|------------|---|
| Version | Spare insert holder, Variant 5 to IEC 61076-3-106 |
| Order No. | 1993540000 |
| Type | IE-PH-AD-V05M-RJ45 |
| GTIN (EAN) | 4050118378610 |
| Qty. | 1 pc(s). |

IE-PH-AD-V05M-RJ45**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 28.1 mm | Depth (inches) | 1.106 inch |
| Height | 21.1 mm | Height (inches) | 0.831 inch |
| Width | 21.2 mm | Width (inches) | 0.835 inch |
| Net weight | 20 g | | |

General data

| | | | |
|--------|---------------|-----------------------|-----|
| Colour | Miscellaneous | Housing main material | PBT |
|--------|---------------|-----------------------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001121 | ETIM 7.0 | EC001121 |
| ETIM 8.0 | EC001121 | ETIM 9.0 | EC001121 |
| ECLASS 9.0 | 27-44-03-90 | ECLASS 9.1 | 27-44-03-90 |
| ECLASS 10.0 | 27-44-03-90 | ECLASS 11.0 | 27-44-03-90 |
| ECLASS 12.0 | 27-44-03-90 | ECLASS 13.0 | 27-44-03-90 |
| ECLASS 14.0 | 27-44-03-90 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key |
| Catalogues | Catalogues in PDF-format |
| Brochures | MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN FL FIELDWIRING EN PI PROFINET CABLING EN |