

EL 100 MM WS 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

Your benefits with MultiMark

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|--------------------|---|
| Version | THM, Device markers, 100 x , white |
| Order No. | 2006720000 |
| Type | EL 100 MM WS 30M |
| GTIN (EAN) | 4050118391497 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

EL 100 MM WS 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|-----------|-----------------|--------------|
| Depth | 0.1 mm | Depth (inches) | 0.004 inch |
| Height | 100 mm | Height (inches) | 3.937 inch |
| Length | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 816 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|-----------------------------|
| Adhesive | Acrylate adhesive | Approval acc. to UL 969 | Yes |
| Colour | white | Halogen | No |
| Length | 30,000 mm | Material | Polyester |
| Number per roll | 1 | Operating temperature range | -40...120 °C |
| Operating temperature range, max. | 120 °C | Operating temperature range, min. | -40 °C |
| UL 94 flammability rating | V-0 | Version | halogen-free, Self-adhesive |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads


| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

EL 100 MM WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



EL 100 MM WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | MM PLUS ROLLER 110 |
| Order No. | 2672590000 |
| GTIN (EAN) | 4050118708097 |
| Qty. | 1 pc(s). |

THM MULTIMARK

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP EXT.RH |
| Order No. | 1302920000 |
| GTIN (EAN) | 4050118102307 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |

EL 100 MM WS 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM 110/360 SW | Version |
| Order No. | 2005070000 | Ink ribbon |
| GTIN (EAN) | 4050118390049 | |
| Qty. | 1 pc(s). | |