

KTB GP XX2620 AB S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

| | |
|------------|---|
| Version | Klippon TB (Terminal Box), flange plate, straight, Height: 250 mm, Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Material: Stainless steel 1.4404, electropolished, silver |
| Order No. | 2023100000 |
| Type | KTB GP XX2620 AB S4 PE |
| GTIN (EAN) | 4050118403350 |
| Qty. | 1 pc(s). |

KTB GP XX2620 AB S4 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 3 mm | Depth (inches) | 0.118 inch |
| Height | 250 mm | Height (inches) | 9.842 inch |
| Width | 167 mm | Width (inches) | 6.575 inch |
| Net weight | 1,006 g | | |

General information

| | | | |
|--------------------|-----------------|-----------------------|--------------------------|
| Gland plates | top, Bottom | Material | Stainless steel 1.4404 |
| Material thickness | 3 mm | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Surface finish | electropolished | | |

General information on accessories

| | | | |
|----------------|------------------------|--------------------|------|
| Material | Stainless steel 1.4404 | Material thickness | 3 mm |
| Surface finish | electropolished | | |

Housing earth

| | |
|-----------------------|---------|
| Flange plate earthing | M6 x 15 |
|-----------------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000211 | ETIM 7.0 | EC000211 |
| ETIM 8.0 | EC000211 | ETIM 9.0 | EC000211 |
| ECLASS 9.0 | 27-14-24-21 | ECLASS 9.1 | 27-18-92-90 |
| ECLASS 10.0 | 27-14-24-21 | ECLASS 11.0 | 27-14-24-21 |
| ECLASS 12.0 | 27-14-24-21 | ECLASS 13.0 | 27-14-24-21 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |