

KCMA-32-600-5A-5VA-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 600 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 1, Split-core current transformer
Order No.	2420720000
Type	KCMA-32-600-5A-5VA-1
GTIN (EAN)	4050118428872
Qty.	1 pc(s).
Manufacturer	MBS AG

Creation date August 29, 2024 8:56:48 PM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

KCMA-32-600-5A-5VA-1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	90 mm	Depth (inches)	3.543 inch
Height	96.4 mm	Height (inches)	3.795 inch
Width	59.2 mm	Width (inches)	2.331 inch
Net weight	427 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-5 °C...50 °C
---------------------	----------------	-----------------------	---------------

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	32.5 mm
Installation location	Indoor use		

Electrical attributes

Load	5 VA	Primary current	600 A
Secondary current	0...5 A	Tolerance class	1

Technical properties

Cable length	0.5 m	Insulation class	E
Nominal frequency	50 Hz	Protection degree	IP20
Thermal rated continuous current I_{thermal}	$1.2 \times I_{\text{rated}}$		

Insulation coordination

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012	Tolerance class	1
----------	--------------------------------------	-----------------	---

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02
ECLASS 14.0	27-21-09-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	instruction sheet german.pdf
Catalogues	Catalogues in PDF-format

KCMA-32-600-5A-5VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

