

**CMA-812-15-5A-7.5VA-0.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

**General ordering data**

Version	Primary current: 1500 A, Secondary current max.: 5 A, Load: 7.5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	<a href="#">2438480000</a>
Type	CMA-812-15-5A-7.5VA-0.5
GTIN (EAN)	4050118450842
Qty.	1 pc(s).
Manufacturer	MBS AG

Creation date June 4, 2024 8:25:47 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**CMA-812-15-5A-7.5VA-0.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	58 mm	Depth (inches)	2.283 inch
Height	198 mm	Height (inches)	7.795 inch
Width	155 mm	Width (inches)	6.102 inch
Net weight	998 g		

**Temperatures**

Storage temperature	-25 °C...40 °C	Operating temperature	-5 °C...40 °C
---------------------	----------------	-----------------------	---------------

**Dimensions of live conductors**

Type of conductor	Insulated conductor only	Round conductor	80 mm
Rail	80 x 120 mm	Installation location	Indoor use

**Electrical attributes**

Load	7.5 VA	Primary current	1,500 A
Secondary current	0...5 A	Tolerance class	0,5

**Technical properties**

Insulation class	E	Nominal frequency	50 Hz
Protection degree	IP20	Thermal rated continuous current $I_{\text{thermal}}$	$1.0 \times I_{\text{rated}}$ , 60 x $I_{\text{rated}}$ for 1 second

**Insulation coordination**

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012	Tolerance class	0,5
----------	--------------------------------------	-----------------	-----

**Classifications**

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Device description – Betriebsanleitung deutsch</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## CMA-812-15-5A-7.5VA-0.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensional drawing

