

WB IK SL PZ2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique inter-changeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

| | |
|------------|----------------------------|
| Version | Screwdriver insert |
| Order No. | 2433240000 |
| Type | WB IK SL PZ2 |
| GTIN (EAN) | 4050118443684 |
| Qty. | 1 pc(s). |

WB IK SL PZ2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Depth | 7 mm | Depth (inches) | 0.276 inch |
| Height | 75 mm | Height (inches) | 2.953 inch |
| Width | 7 mm | Width (inches) | 0.276 inch |
| Net weight | 11.7 g | | |

Technical data

| | |
|------------------------|---|
| Description of article | VDE insulated interchangeable bit for crosshead screws, Pozidrive, size 2 |
|------------------------|---|

Screwing tools

| | | | |
|----------------------|-----------|------|---|
| Form | Pozidrive | Size | 2 |
| Torque setting, max. | 5.5 Nm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002115 | ETIM 7.0 | EC002115 |
| ETIM 8.0 | EC003864 | ETIM 9.0 | EC003864 |
| ECLASS 9.1 | 21-04-04-90 | ECLASS 10.0 | 21-04-04-90 |
| ECLASS 11.0 | 21-04-42-03 | ECLASS 12.0 | 21-04-42-03 |
| ECLASS 13.0 | 21-04-42-03 | | |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | Manufacturer's Declaration - Slim Bits |
| Catalogues | Catalogues in PDF-format |