


**HS 1.6-4.8/12 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 1.6 - 4.8 mm, 12.7 x 8.7 mm, yellow
Order No.	<a href="#">2526100000</a>
Type	HS 1.6-4.8/12 MM Y
GTIN (EAN)	4050118537253
Qty.	4,000 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

**HS 1.6-4.8/12 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.7 mm	Depth (inches)	0.028 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	8.7 mm	Width (inches)	0.343 inch
Net weight	0.158 g		

**Temperatures**

Operating temperature range	-55...135 °C
-----------------------------	--------------

**General data**

Colour	yellow	Halogen	Yes
Material	Polyolefine	Number per roll	4,000
Operating temperature range	-55...135 °C	Operating temperature range, max.	135 °C
Operating temperature range, min.	-55 °C	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
Width	8.7 mm		

**Conductor and cable markers**

Conductor O.D.	1.6 - 4.8 mm	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	1.6 mm	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Cross-section for connected wire	0.75 - 4 mm <sup>2</sup>
Halogen	Yes	Rate of shrinkage	3:1
Recommended shrinking temperature	90 °C		

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**HS 1.6-4.8/12 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

