

**HDC 06B ALU EMC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The new Weidmüller RockStar® IP65 EMV enclosures are ideally suited for use in the harshest environmental conditions and provide protection against electromagnetic interference. A heavy-duty connector consists of a connector insert and its protective housing. The new plastic straps are easy to lock and can be replaced at any time. All Weidmüller RockStar® enclosures are made of high quality die-cast aluminium. This makes them impact- and corrosion-resistant, yet compact and lightweight.

**General ordering data**

Version	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, End-locking clamp replaceable
Order No.	<a href="#">2542230000</a>
Type	HDC 06B ALU EMC
GTIN (EAN)	4050118648720
Qty.	1 pc(s).

## HDC 06B ALU EMC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	80 mm	Depth (inches)	3.15 inch
Height	30 mm	Height (inches)	1.181 inch
Width	45 mm	Width (inches)	1.772 inch
Net weight	88 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## General data

EMC housings	Yes	Housing main material	diecast aluminium
Material of locking element	PA 66/6, Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	UL 94 flammability rating	V-0

## Version

BG	3	Clamp version	End-locking clamp
Colour (RAL)	RAL 9011	Cover	without cover
Design of housing		Design of locking system	End-locking clamp, lower side, End-locking clamp replaceable
	Bulkhead housing		
Sealing	FPM	Size	3
Suitable for ModuPlug®	Yes	Top part/bottom part/lid	lower part
Type	Bulkhead (feed-through)		

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Petrol
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Resistant
Substance	Ozone
Chemical resistance	Resistant

## HDC 06B ALU EMC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



UL File Number Search	UL Website
-----------------------	------------

Certificate No. (cURus)	E92202
-------------------------	--------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
------------------	---------------------------------

Product Change Notification	<a href="#">20220214 Technical change to HDC housings</a> <a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a>
-----------------------------	--

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## HDC 06B ALU EMC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

