

IE-FC-IP-PWB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert plate, unshielded, 1x Power
Order No.	2548060000
Type	IE-FC-IP-PWB
GTIN (EAN)	4050118557596
Qty.	1 pc(s).

IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	19.5 mm	Height (inches)	0.768 inch
Width	51.5 mm	Width (inches)	2.028 inch
Length	90.5 mm	Length (inches)	3.563 inch
Net weight	14.825 g		

Temperatures

Operating temperature	-40 °C...70
-----------------------	-------------

General data

Material	Polycarbonate PC	Product type	Insert plate, unshielded
----------	------------------	--------------	--------------------------

Inserts

Insert Power large	1
--------------------	---

General standards

Certificate No. (CSA)	2000039-80039714	Certificate No. (cURus)	E223801
-----------------------	------------------	-------------------------	---------

Classifications

ETIM 6.0	EC000456	ETIM 7.0	EC000456
ETIM 8.0	EC000456	ETIM 9.0	EC000456
ECLASS 9.0	27-18-28-06	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-18-28-06	ECLASS 11.0	27-18-28-06
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-4318-8088-c28f019e7f77

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Downloads

Engineering Data	CAD data – STEP
User Documentation	Designation key / Type key
Catalogues	Catalogues in PDF-format

IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Power sockets



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Type	IE-FCI-PWB-FR	Version
Order No.	1450750000	FrontCom, Insert Power large, Type E, Socket connector, FR
GTIN (EAN)	4050118255706	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-CH	Version
Order No.	1450780000	FrontCom, Insert Power large, Type J, Socket connector, CH
GTIN (EAN)	4050118255553	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-IND	Version
Order No.	2500710000	FrontCom, Insert Power large, Type D, Socket connector, IN
GTIN (EAN)	4050118526745	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-DE	Version
Order No.	1450730000	FrontCom, Insert Power large, Type F, Socket connector, DE
GTIN (EAN)	4050118255546	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-GB	Version
Order No.	1450770000	FrontCom, Insert Power large, Type G, Socket connector, GB
GTIN (EAN)	4050118255577	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-AU-10A	Version
Order No.	1546590000	FrontCom, Insert Power large, Type I, Socket connector, AU, 10 A
GTIN (EAN)	4050118351842	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-CN	Version
Order No.	1450790000	FrontCom, Insert Power large, Type I, Socket connector, CN
GTIN (EAN)	4050118255386	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-FR-OR	Version
Order No.	2007230000	FrontCom, Insert Power large, Type E, Socket connector, FR, orange
GTIN (EAN)	4050118392135	
Qty.	1 pc(s).	
Type	IE-FCI-PWS-IT	Version
Order No.	1450810000	FrontCom, Insert Power small, Type L, Socket connector, IT, EU
GTIN (EAN)	4050118255720	
Qty.	1 pc(s).	

IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	IE-FCI-PWB-AU	Version
Order No.	1450830000	FrontCom, Insert Power large, Type I, Socket connector, AU, 15 A
GTIN (EAN)	4050118255591	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-ISR	Version
Order No.	2531060000	FrontCom, Insert Power large, Type H, Socket connector, ISR
GTIN (EAN)	4050118541175	
Qty.	1 pc(s).	
Type	IE-FCI-PWB-FR/B/CZ	Version
Order No.	2426700000	FrontCom, Insert Power large, Type E, Socket connector, FR, CZ
GTIN (EAN)	4050118435139	
Qty.	1 pc(s).	

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 7/20 SIRIUS MC NE WS	Version
Order No.	1736181044	ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable
GTIN (EAN)	4008190985950	
Qty.	200 pc(s).	


IE-FC-IP-PWB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Accessories for FrontCom Vario****General ordering data**

Type	IE-FC-PWPC	Version
Order No.	1450820000	FrontCom, Touch-safe protection
GTIN (EAN)	4050118255584	
Qty.	1 pc(s).	

Slotted screwdriver

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1.
ChromTop tip, SoftFinish grip

General ordering data

Type	SDS 0.4X2.5X75	Version
Order No.	9009030000	Screwdriver, Screwdriver
GTIN (EAN)	4032248266944	
Qty.	1 pc(s).	