

CD-FLEX 40X40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|--|
| Version | Flexible wiring duct, 40 mm x 40 mm, 5.00 mm x 7.50 mm, 500 mm |
| Order No. | 2562800000 |
| Type | CD-FLEX 40X40 |
| GTIN (EAN) | 4050118571547 |
| Qty. | 50 pc(s). |

CD-FLEX 40X40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|-------------|
| Height | 40 mm | Height (inches) | 1.575 inch |
| Width | 40 mm | Width (inches) | 1.575 inch |
| Length | 500 mm | Length (inches) | 19.685 inch |
| Net weight | 71 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -15...80 °C |
|-----------------------------|-------------|

General information

| | | | |
|----------------------|----------------------------|-----------------------------|---------------|
| Colour | grey (similar to RAL 7001) | Flexible wiring duct | Yes |
| Lid | No | Material | Polypropylene |
| Non-tracking | Yes | Operating temperature range | -15...80 °C |
| Slit gap | 7.5 mm | Slit width | 5 mm |
| Type of mounting | With adhesive | UL 94 flammability rating | V-2 |
| Usable cross-section | 1,310 mm ² | Version of side panel | slotted |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000012 | ETIM 7.0 | EC000012 |
| ETIM 8.0 | EC000012 | ETIM 9.0 | EC000012 |
| ECLASS 9.1 | 27-40-07-03 | ECLASS 10.0 | 27-40-07-03 |
| ECLASS 11.0 | 27-40-07-03 | ECLASS 12.0 | 27-40-07-03 |
| ECLASS 13.0 | 27-40-07-03 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|