

P BAG SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Tools, Accessories
Order No.	2579460000
Type	P BAG SET 7
GTIN (EAN)	4050118648379
Qty.	1 pc(s).

P BAG SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	170 mm	Depth (inches)	6.693 inch
Height	50 mm	Height (inches)	1.969 inch
Width	260 mm	Width (inches)	10.236 inch
Net weight	1,220.8 g		

Technical data

Description of article	Toolbag, fitted
------------------------	-----------------

Classifications

ETIM 6.0	EC000181	ETIM 7.0	EC000181
ETIM 8.0	EC000181	ETIM 9.0	EC000181
ECLASS 9.0	21-10-01-90	ECLASS 9.1	21-10-01-90
ECLASS 10.0	21-10-01-90	ECLASS 11.0	21-10-01-90
ECLASS 12.0	21-10-01-90	ECLASS 13.0	21-10-01-90

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Downloads

Catalogues	Catalogues in PDF-format
------------	--

P BAG SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****unfitted**

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Type	P BAG	Version
Order No.	2548180000	Tools, Accessories
GTIN (EAN)	4050118557916	
Qty.	1 pc(s).	

Tools

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX 16	Version
Order No.	9005610000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190183875	
Qty.	1 pc(s).	

P BAG SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crimping tools****Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 16	Version
Order No.	9012600000	Pressing tool, Crimping tool for wire-end ferrules, 6mm ² , 16mm ² ,
GTIN (EAN)	4008190035440	Indent crimp
Qty.	1 pc(s).	

Cutting tools

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 8	Version
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 pc(s).	

P BAG SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Non-contact voltage tester**

- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Type	VT LCL	Version
Order No.	2436670000	Testing tools, Cable detector
GTIN (EAN)	4050118450033	
Qty.	1 pc(s).	