

P BAG SET 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | |
|------------|----------------------------|
| Version | Tools, Accessories |
| Order No. | 2579490000 |
| Type | P BAG SET 10 |
| GTIN (EAN) | 4050118628074 |
| Qty. | 1 pc(s). |

P BAG SET 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|-----------|-----------------|-------------|
| Depth | 170 mm | Depth (inches) | 6.693 inch |
| Height | 50 mm | Height (inches) | 1.969 inch |
| Width | 260 mm | Width (inches) | 10.236 inch |
| Net weight | 1,289.1 g | | |

Technical data

| | |
|------------------------|-----------------|
| Description of article | Toolbag, fitted |
|------------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000181 | ETIM 7.0 | EC000181 |
| ETIM 8.0 | EC000181 | ETIM 9.0 | EC000181 |
| ECLASS 9.0 | 21-10-01-90 | ECLASS 9.1 | 21-10-01-90 |
| ECLASS 10.0 | 21-10-01-90 | ECLASS 11.0 | 21-10-01-90 |
| ECLASS 12.0 | 21-10-01-90 | ECLASS 13.0 | 21-10-01-90 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

P BAG SET 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories**Tools**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | | |
|------------|----------------------------|-----------------------------------|
| Type | STRIPAX ULTIMATE | Version |
| Order No. | 1468880000 | Tools, Stripping and cutting tool |
| GTIN (EAN) | 4050118274158 | |
| Qty. | 1 pc(s). | |

Non-contact voltage tester

- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

| | | |
|------------|----------------------------|-------------------------------|
| Type | VT LCL | Version |
| Order No. | 2436670000 | Testing tools, Cable detector |
| GTIN (EAN) | 4050118450033 | |
| Qty. | 1 pc(s). | |

P BAG SET 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****unfitted**

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | | |
|------------|----------------------------|--------------------|
| Type | P BAG | Version |
| Order No. | 2548180000 | Tools, Accessories |
| GTIN (EAN) | 4050118557916 | |
| Qty. | 1 pc(s). | |

Cutting tools

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | KT 8 | Version |
| Order No. | 9002650000 | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163 | |
| Qty. | 1 pc(s). | |

P BAG SET 10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimping tools

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | | |
|------------|----------------------------|---|
| Type | PZ 10 SQR | Version |
| Order No. | 1445080000 | Crimping tool for wire-end ferrules, 0.14mm ² , 10mm ² , Square crimp |
| GTIN (EAN) | 4050118250152 | |
| Qty. | 1 pc(s). | |