

CRIMPFIX R VARIO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	2580000000
Type	CRIMPFIX R VARIO
GTIN (EAN)	4050118605846
Qty.	1 pc(s).

CRIMPFIX R VARIO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	485 mm	Depth (inches)	19.094 inch
Height	565 mm	Height (inches)	22.244 inch
Width	335 mm	Width (inches)	13.189 inch
Net weight	25,265 g		

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	Linked wire-end ferrules
Crimping	Trapezoidal	Crimping length	8/10 mm
Drive	Electropneumatic	Electrical connection	100 - 240 V / 50/60 Hz / 16 VA
Insertion length, min.	27 mm	Length of wire-end ferrule	14/16 mm
Pulse time	approx. 2 s	Stripping range	0.5 - 2.5 mm ² (~ AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Approvals

Approvals



ROHS Conform

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

CRIMPFIX R VARIO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories / replacement parts**

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	AIMESA CF U/L/LS SK TIN	Version
Order No.	1283530000	Automatic machines, Replacement part
GTIN (EAN)	4050118073676	
Qty.	1 pc(s).	
Type	CRIMPFIX R VARIO PZ3	Version
Order No.	2912420000	Automatic machines, Automatic stripper and crimper
GTIN (EAN)	4099986535992	
Qty.	1 pc(s).	