

IE-USB-3.0-A-A-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables

General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 3 m
Order No.	2581730030
Type	IE-USB-3.0-A-A-3M
GTIN (EAN)	4050118630534
Qty.	1 pc(s).

IE-USB-3.0-A-A-3M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	3 m	Length (inches)	118.11 inch
Net weight	140 g		

Temperatures

Operating temperature	-15 °C...80 °C
-----------------------	----------------

Technical specifications for cable

Sheathing colour	blue
------------------	------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)	Material sheath	PVC
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Sheathing colour	blue		

Plug

Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded	Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
-----------	--	------------	--

Plug, left

Contact surface, plug, left	Gold over nickel	Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
-----------------------------	------------------	-----------	--

Plug, right

Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
------------	--

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ETIM 9.0	EC001408
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

Approvals

ROHS	Conform
------	---------

IE-USB-3.0-A-A-3M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Product Change Notification

[Technical change sheathing colour of USB cable 3.0](#)

[Technische Änderung Mantelfarbe des USB-Kabel 3.0](#)

Catalogues

[Catalogues in PDF-format](#)