

CD-BO 40X100 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct, 40 mm x 100 mm, 8.00 mm x 12.00 mm, 2000 mm
Order No.	2588800000
Type	CD-BO 40X100 8/12 GY
GTIN (EAN)	4050118602876
Qty.	16 m

CD-BO 40X100 8/12 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	40 mm	Height (inches)	1.575 inch
Width	100 mm	Width (inches)	3.937 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	706 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

General information

Colour	grey	Flexible wiring duct	No
Floor rails	1	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Slit gap	12 mm
Slit width	8 mm	Standards	In accordance with DIN EN 50085
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	3,350 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03	ECLASS 14.0	27-40-07-03

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CD-BO 40X100 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

CD-BO 40X100 8/12 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

T-Form

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-RETT 40	Version
Order No.	2554090000	Cable duct T-form binder
GTIN (EAN)	4050118564211	
Qty.	40 pc(s).	
Type	CD-RETT 60	Version
Order No.	2554100000	Cable duct T-form binder
GTIN (EAN)	4050118564228	
Qty.	25 pc(s).	

Separator

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-SE 40/2	Version
Order No.	2553950000	Cable duct separator, 40 mm x
GTIN (EAN)	4050118564082	
Qty.	30 pc(s).	
Type	CD-SE 40	Version
Order No.	2553970000	Cable duct separator, 40 mm x
GTIN (EAN)	4050118564105	
Qty.	60 pc(s).	

CD-BO 40X100 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Flat**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RET 100/120	Version
Order No.	2554060000	Cable duct binder
GTIN (EAN)	4050118564181	
Qty.	250 pc(s).	

Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

CD-BO 40X100 8/12 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	
Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	

Metric

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-LID 100 GY	Version
Order No.	2590000000	Cable duct cover, 100 mm
GTIN (EAN)	4050118600766	
Qty.	2 m	

CD-BO 40X100 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Rivet and cover**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	
Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	
Type	CD-SCCV	Version
Order No.	2554000000	Cable duct screw cover
GTIN (EAN)	4050118564136	
Qty.	1,000 pc(s).	