

**CD-HF 75X37.5 5/7.5 LTGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

DIN EN 4545-2



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Version	Halogen-free cable duct, 75 mm x 37.5 mm, 5.00 mm x 7.50 mm, 2000 mm
Order No.	<a href="#">2589750000</a>
Type	CD-HF 75X37.5 5/7.5 LTGY
GTIN (EAN)	4050118603323
Qty.	32 m

## CD-HF 75X37.5 5/7.5 LTGY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	75 mm	Height (inches)	2.953 inch
Width	37.5 mm	Width (inches)	1.476 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	434 g		

## Temperatures

Operating temperature range	-25...105 °C
-----------------------------	--------------

## General information

Colour	Light Grey	Flexible wiring duct	No
Halogen	No	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PC-ABS
Non-tracking	Yes	Operating temperature range	-25...105 °C
Slit gap	7.5 mm	Slit width	5 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	2,370 mm <sup>2</sup>
Version of side panel	slotted		

## Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03		

## Environmental Product Compliance

REACH SVHC	/
------------	---

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**CD-HF 75X37.5 5/7.5 LTGY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

---

---

**CD-HF 75X37.5 5/7.5 LTGY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Side arm**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	<a href="#">2554080000</a>	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

**Light grey**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-LID 37.5 LTGY	Version
Order No.	<a href="#">2589220000</a>	Cable duct cover, 37.5 mm
GTIN (EAN)	4050118602654	
Qty.	2 m	

## CD-HF 75X37.5 5/7.5 LTGY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

## General ordering data

Type	CD-LBK	Version
Order No.	<a href="#">2554120000</a>	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	
Type	CD-LB	Version
Order No.	<a href="#">2562680000</a>	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBH	Version
Order No.	<a href="#">2562850000</a>	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	

## Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



## General ordering data

Type	EXRV-T 4.5	Version
Order No.	<a href="#">2562720000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	<a href="#">2562710000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV 6.5	Version
Order No.	<a href="#">2562690000</a>	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	

### CD-HF 75X37.5 5/7.5 LTGY

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	EXRV 4.5	Version
Order No.	<a href="#">2562700000</a>	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	