

CD-HF 75X50 5/7.5 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

DIN EN 4545-2



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Halogen-free cable duct, 75 mm x 50 mm, 5.00 mm x 7.50 mm, 2000 mm
Order No.	2589780000
Type	CD-HF 75X50 5/7.5 LTGY
GTIN (EAN)	4050118603347
Qty.	24 m

CD-HF 75X50 5/7.5 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	75 mm	Height (inches)	2.953 inch
Width	50 mm	Width (inches)	1.969 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	437.5 g		

Temperatures

Operating temperature range	-25...105 °C
-----------------------------	--------------

General information

Colour	Light Grey	Flexible wiring duct	No
Halogen	No	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PC-ABS
Non-tracking	Yes	Operating temperature range	-25...105 °C
Slit gap	7.5 mm	Slit width	5 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	3,200 mm ²
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CD-HF 75X50 5/7.5 LTGY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

CD-HF 75X50 5/7.5 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Side arm**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	

CD-HF 75X50 5/7.5 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Light grey**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LID 50 LTGY	Version
Order No.	2589200000	Cable duct cover, 50 mm
GTIN (EAN)	4050118602616	
Qty.	2 m	

Flat

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-RET 60	Version
Order No.	2554030000	Cable duct binder
GTIN (EAN)	4050118564167	
Qty.	500 pc(s).	

CD-HF 75X50 5/7.5 LTGY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Marking**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	