

**CD-BO 60X100 8/12 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Version	Cable duct floor duct, 60 mm x 100 mm, 8.00 mm x 12.00 mm, 2000 mm
Order No.	<a href="#">2589760000</a>
Type	CD-BO 60X100 8/12 GY
GTIN (EAN)	4050118600995
Qty.	20 m

## CD-BO 60X100 8/12 GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	60 mm	Height (inches)	2.362 inch
Width	100 mm	Width (inches)	3.937 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	885 g		

## Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

## General information

Colour	grey	Flexible wiring duct	No
Floor rails	1	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Slit gap	12 mm
Slit width	8 mm	Standards	In accordance with DIN EN 50085
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	5,320 mm <sup>2</sup>	Version of side panel	slotted

## Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03	ECLASS 14.0	27-40-07-03

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**CD-BO 60X100 8/12 GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

---

---

## CD-BO 60X100 8/12 GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



## General ordering data

Type	EXRV-T 6.5	Version
Order No.	<a href="#">2562710000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV 6.5	Version
Order No.	<a href="#">2562690000</a>	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV 4.5	Version
Order No.	<a href="#">2562700000</a>	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	<a href="#">2562720000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	
Type	CD-SCCV	Version
Order No.	<a href="#">2554000000</a>	Cable duct screw cover
GTIN (EAN)	4050118564136	
Qty.	1,000 pc(s).	

## Side arm

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



## General ordering data

Type	CD-RETA	Version
Order No.	<a href="#">2554080000</a>	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

**CD-BO 60X100 8/12 GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****T-Form**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETT 40	Version
Order No.	<a href="#">2554090000</a>	Cable duct T-form binder
GTIN (EAN)	4050118564211	
Qty.	40 pc(s).	
Type	CD-RETT 60	Version
Order No.	<a href="#">2554100000</a>	Cable duct T-form binder
GTIN (EAN)	4050118564228	
Qty.	25 pc(s).	

**Metric**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-LID 100 GY	Version
Order No.	<a href="#">2590000000</a>	Cable duct cover, 100 mm
GTIN (EAN)	4050118600766	
Qty.	2 m	

## CD-BO 60X100 8/12 GY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

## General ordering data

Type	CD-LBH	Version
Order No.	<a href="#">2562850000</a>	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	
Type	CD-LB	Version
Order No.	<a href="#">2562680000</a>	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	<a href="#">2554120000</a>	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	

## Flat

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



## General ordering data

Type	CD-RET 100/120	Version
Order No.	<a href="#">2554060000</a>	Cable duct binder
GTIN (EAN)	4050118564181	
Qty.	250 pc(s).	

## CD-BO 60X100 8/12 GY

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Separator



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

## General ordering data

Type	CD-SE 60	Version
Order No.	<a href="#">2553960000</a>	Cable duct separator, 60 mm x
GTIN (EAN)	4050118564099	
Qty.	50 pc(s).	