

WIL-NT-STANDARD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Power supply IP65 for WIL standard family 85V-264V AC
input, 24V DC output 400mA

General ordering data

Order No.	2598350000
Type	WIL-NT-STANDARD
GTIN (EAN)	4050118611168
Qty.	1 pc(s).

WIL-NT-STANDARD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	32 mm	Height (inches)	1.26 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	292 g		

Temperatures

Operating temperature	-30 - 50°C
-----------------------	------------

Cable technical specifications

Cable Material	TPE	Sheathing colour	black
Cable length	3	Core cross-section	0.75 mm ²

Electric data

Rated voltage	24 V DC	Rated current	1,10 A
---------------	---------	---------------	--------

General technical data

Type of mounting	Screw mounting	Protection degree	IP65 when locked
------------------	----------------	-------------------	------------------

Material data

Housing main material	PBT	Threaded ring material	Nickel-plated CuZn
-----------------------	-----	------------------------	--------------------

Power supply / input

Input frequency	47 - 63 Hz	Input fuse (internal)	Yes
Version	Cable end open	Connecting thread	without
Circuitry	Blue -, Black +		

Power supply / output

Connection system	Screw connection	Output current, max.	0.4 A
Version	Socket connector	Connecting thread	M12
Circuitry	PIN 3: - (blue), PIN 4: + (black)		

Power supply / safety

Safety standard	SELV according to EN 60950, EN 61347-2-13	Short-circuit protection	Yes
Overload protection	Yes	Protection against over-heating	Yes
Protection class	II	Safety extra-low voltage	Yes

Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ETIM 9.0	EC002540
ECLASS 9.0	27-04-07-01	ECLASS 9.1	27-04-07-01
ECLASS 10.0	27-04-07-01	ECLASS 11.0	27-04-07-01
ECLASS 12.0	27-04-07-01	ECLASS 13.0	27-04-07-01
ECLASS 14.0	27-04-07-01		

WIL-NT-STANDARD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

REACH SVHC

/

RoHS Compliance Status

Compliant without exemption

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

WIL-NT-STANDARD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

