

PRO CASE CAB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Tool case with contents
Order No.	2602250000
Type	PRO CASE CAB
GTIN (EAN)	4050118613018
Qty.	1 pc(s).

PRO CASE CAB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	170 mm	Depth (inches)	6.693 inch
Height	400 mm	Height (inches)	15.748 inch
Width	480 mm	Width (inches)	18.898 inch
Net weight	6,162 g		

Technical data

Description of article	Tool case
------------------------	-----------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-10-01-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl

Downloads

Catalogues	Catalogues in PDF-format
------------	--

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Screwdriver Sets



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDI SET SLIM S3.5-6.5/P ...	Version
Order No.	2749580000	Mounting tool
GTIN (EAN)	4050118896329	
Qty.	1 pc(s).	

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version
Order No.	9005000000	Tools, Stripping and cutting tool
GTIN (EAN)	4008190072506	
Qty.	1 pc(s).	

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Continuity testers



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Type	VT CTL	Version
Order No.	2436690000	Testing tools, Testing device
GTIN (EAN)	4050118450040	
Qty.	1 pc(s).	

Socket wrench sets



Allen key made from fully hardened, high-alloy chromium-vanadium- steel, acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.

General ordering data

Type	SK WSD-S 1,5-10,0	Version
Order No.	9008850000	Mounting tool
GTIN (EAN)	4032248266609	
Qty.	1 pc(s).	
Type	TH-S 9-40	Version
Order No.	9008880000	socket wrenches
GTIN (EAN)	4032248266630	
Qty.	1 pc(s).	

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	FRZ S 160	Version
Order No.	9046370000	Pliers
GTIN (EAN)	4032248357673	
Qty.	1 pc(s).	

Non-contact voltage tester



- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

General ordering data

Type	VT LCL	Version
Order No.	2436670000	Testing tools, Cable detector
GTIN (EAN)	4050118450033	
Qty.	1 pc(s).	

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Measuring instruments



Precision tools from Weidmüller are in use worldwide. Weidmüller takes this responsibility seriously and offers comprehensive services. Tools should still function perfectly even after many years of constant use. Weidmüller therefore offers its customers the "Tool Certification" service. This technical testing routine allows Weidmüller to guarantee the proper functioning and quality of its tools.

General ordering data

Type	FLEXIMET 5 M	Version
Order No.	2534210000	Measuring tape
GTIN (EAN)	4050118545975	
Qty.	1 pc(s).	

Empty



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Type	PRO CASE LEER	Version	Packaging
Order No.	9202470000	Assortment box	Case
GTIN (EAN)	4032248495788		
Qty.	1 pc(s).		

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Cabinet keys



Crimped conductors are fixed in their respective wiring spaces by screws or a direct plug-in feature. Weidmüller can supply a wide range of tools for screwing.

General ordering data

Type	CROSS-KEY UNIVERSAL	Version
Order No.	9918130000	Universal key
GTIN (EAN)	4032248371112	
Qty.	1 pc(s).	

VDE-insulated combination pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	KBZ 180	Version
Order No.	9046290000	Pliers
GTIN (EAN)	4032248356485	
Qty.	1 pc(s).	

PRO CASE CAB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crimping tools****Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 10 HEX	Version
Order No.	1445070000	Crimping tool for wire-end ferrules, 0.25mm ² , 10mm ² , Hexagonal
GTIN (EAN)	4050118250312	crimp
Qty.	1 pc(s).	

with LCD Display

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

Type	VT DIGI PRO	Version
Order No.	9918870000	Testing tools, 2-pole voltage tester
GTIN (EAN)	4032248405756	
Qty.	1 pc(s).	

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 8	Version
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 pc(s).	

Assortment of wire end ferrules with plastic collar



Box filled with wire end ferrules with plastic collar:

- in Weidmüller colour code
- DIN colour code

General ordering data

Type	H-BOX 0,5-2,5QMM DIN	Version	Packaging
Order No.	9025430000	Assortment of wire end ferrules, Box, Colour code: DIN	Box
GTIN (EAN)	4008190337162		
Qty.	1 pc(s).		

PRO CASE CAB

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Type	STRIPPER ROUND TOP	Version
Order No.	9918050000	Sheathing strippers
GTIN (EAN)	4032248359165	
Qty.	1 pc(s).	

VDE-insulated diagonal-cutting pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose. Weidmüller offers a complete line of pliers which comply with national and international testing standards. All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	SE HD 180	Version
Order No.	9046330000	Diagonal-cutting pliers
GTIN (EAN)	4032248357635	
Qty.	1 pc(s).	

PRO CASE CAB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Combined screwing and cutting tool "Swiftly®"**

Combined cutting/screwing tool: Swiftly® and Swiftly® set for clean cutting of copper cables up to 1.5 mm² (solid) and 2.5 mm² (flexible)

**General ordering data**

Type	SWIFTY SET	Version
Order No.	9006060000	Cutting and screwing-tool, Cutting tool for one-hand operation
GTIN (EAN)	4032248257638	
Qty.	1 pc(s).	