

**SRQB 4/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Screwable cross-connections are easy to mount and de-mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, black, 41 A, Number of poles: 3, Pitch in mm (P): 11.00, Insulated: Yes, Width: 28 mm
Order No.	<a href="#">2615230000</a>
Type	SRQB 4/3
GTIN (EAN)	4050118653656
Qty.	50 pc(s).

**SRQB 4/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	3.5 mm	Depth (inches)	0.138 inch
Height	28.4 mm	Height (inches)	1.118 inch
Width	28 mm	Width (inches)	1.102 inch
Net weight	0.54 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	PA	Colour	black
----------	----	--------	-------

**System specifications**

Version	Cross-connector
---------	-----------------

**Additional technical data**

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

**Cross-connector**

Rated current, multi-pole	41 A	Type	Cross-connector
---------------------------	------	------	-----------------

**Dimensions**

Pitch in mm (P)	11 mm
-----------------	-------

**General**

Number of poles	3
-----------------	---

**Rating data**

Rated current	41 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## SRQB 4/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>