

HDC MPN 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Pneumatic module
Order No.	2637320000
Type	HDC MPN 2
GTIN (EAN)	4050118767520
Qty.	1 pc(s).

HDC MPN 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.55 g
------------	--------

Temperatures

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

General data

Material	Polycarbonate, glass fibre reinforced	Number of poles	2
Plugging cycles	≥ 500	Required plug-in slots	1
Series	ModuPlug	Type	Male, Female
UL 94 flammability rating	V-0		

Pneumatic module

Module operating pressure	8 bar	Inner hose diameter, min.	6 mm
Inner hose diameter, max.	6 mm		

Version

Type of connection	Hose connection (pneumatic)
--------------------	-----------------------------

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC000438
ETIM 8.0	EC000438	ETIM 9.0	EC000438
ECLASS 9.0	27-44-02-20	ECLASS 9.1	27-44-02-20
ECLASS 10.0	27-44-02-20	ECLASS 11.0	27-44-02-20
ECLASS 12.0	27-44-02-20	ECLASS 13.0	27-44-02-20

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

Downloads




Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

HDC MPN 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HDC MPN 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Pneumatic contacts


Make your connections fit for the future With the advanced solutions from RockStar® ModuPlug

Industrial applications are becoming increasingly complex. The demands being made of the connectivity used are growing at the same time. Functionality in the smallest of installation spaces, safe installation and a fast retrofitting process are just some of the product properties being called for. Not only does our RockStar® ModuPlug modular plug-in connector system meet current market requirements; it has been specially designed with the future in mind too. Using the individual modules, you combine all the necessary functions for power, signal and data transmission in a single interface. Thanks to the new variety of module sizes, you can fit more applications than ever before in one plug-in connector. The modules reduce the amount of space required and cut costs when compared with fixed-pole inserts and other modular plug-in connector systems. The sophisticated frames and modules can be installed with extreme ease and integrated into HDC enclosures with the IP65 and IP68 protection classes. You can even use the RockStar® ModuPlug to supplement existing applications without any need to make system adjustments. As an experienced Industrial Connectivity partner, Weidmüller offers ultra-modern connectivity with maximum reliability. So you can create customised solutions for future-proof connections with RockStar® too.

General ordering data

Type	HDC MPN 6.0 SOF	Version
Order No.	2637400000	Pneumatic contact, Contact with valve: Yes
GTIN (EAN)	4050118654547	
Qty.	10 pc(s).	
Type	HDC MPN 6.0 F	Version
Order No.	2637390000	Pneumatic contact, Contact with valve: No
GTIN (EAN)	4050118654530	
Qty.	10 pc(s).	
Type	HDC MPN 6.0 M	Version
Order No.	2637350000	Pneumatic contact, Contact with valve: No
GTIN (EAN)	4050118654615	
Qty.	10 pc(s).	