

**CD 40X80 4/6 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Well-structured and protected wiring provides the basis for installation, maintenance, and safe operation. Those requirements apply in particular for explosion-protected areas. According to DIN EN 60079-14 these wiring ducts are suitable for cables containing intrinsically safe circuits.

**General ordering data**

Version	40 mm x 80 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	<a href="#">2662470000</a>
Type	CD 40X80 4/6 BL
GTIN (EAN)	4050118684971
Qty.	24 m

**CD 40X80 4/6 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	40 mm	Height (inches)	1.575 inch
Width	80 mm	Width (inches)	3.15 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	567 g		

**Temperatures**

Operating temperature range	-5...60 °C
-----------------------------	------------

**General information**

Colour	blue	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Operating temperature range	-5...60 °C
Slit gap	6 mm	Slit width	4 mm
Standards	In accordance with DIN EN 50085	UL 94 flammability rating	V-0
Version of side panel	slotted		

**Classifications**

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ECLASS 9.1	27-40-07-03	ECLASS 10.0	27-40-07-03
ECLASS 11.0	27-40-07-03	ECLASS 12.0	27-40-07-03
ECLASS 13.0	27-40-07-03	ECLASS 14.0	27-40-07-03

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**CD 40X80 4/6 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Flat**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RET 80	Version
Order No.	<a href="#">2554050000</a>	Cable duct binder
GTIN (EAN)	4050118564174	
Qty.	400 pc(s).	

**Side arm**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	<a href="#">2554080000</a>	Cable duct binder arm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	

## CD 40X80 4/6 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

## General ordering data

Type	CD-LB	Version
Order No.	<a href="#">2562680000</a>	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	<a href="#">2554120000</a>	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	
Type	CD-LBH	Version
Order No.	<a href="#">2562850000</a>	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	

## Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



## General ordering data

Type	EXRV 6.5	Version
Order No.	<a href="#">2562690000</a>	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	<a href="#">2562710000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	<a href="#">2562720000</a>	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	

### CD 40X80 4/6 BL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	EXRV 4.5	Version
Order No.	<a href="#">2562700000</a>	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	