

IE-PIC-M12X-P-22/26**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Machined precision crimp contacts for M12X

General ordering data

Version	Contact, Pin
Order No.	2664880000
Type	IE-PIC-M12X-P-22/26
GTIN (EAN)	4050118765342
Qty.	100 pc(s).

IE-PIC-M12X-P-22/26**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.047 g
------------	---------

Technical data customisable plug-in connectors

Coding	X-coded	Conductor cross-section, max.	0.14 mm ²
Conductor cross-section, min.	0.34 mm ²	Connection cross-section	AWG 22 - AWG 26
Contact material	Copper alloy, Gold-plated	Number of poles	4
Rated current	1 A		

General Info

Number of poles	4	Connection 1	M12 Contact
Connection 2	Crimp	Contact material	Copper alloy, Gold-plated

Electrical properties

Contact resistance	≤ 10 mΩ
--------------------	---------

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

ROHS	Conform
------	---------

Downloads


Catalogues	Catalogues in PDF-format
------------	------------------------------------------

IE-PIC-M12X-P-22/26

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



IE-PIC-M12X-P-22/26**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****...for M12**

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SAI-TMCSK	Version
Order No.	1381690000	Pressing tool, 4-indent crimp
GTIN (EAN)	4050118183870	
Qty.	1 pc(s).	