

**SAI-M12-KSC-18/20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

The crimp connection is characterised by high functional reliability. With this connection technology, the conductor is crimped to the contact and then engaged in the contact carrier. The connection between the conductor and crimp is vibration-resistant and boasts long-term stability. Crimp contacts are to be ordered separately.

**General ordering data**

Version	Contact, Pin
Order No.	<a href="#">2664840000</a>
Type	SAI-M12-KSC-18/20
GTIN (EAN)	4050118755091
Qty.	100 pc(s).

**SAI-M12-KSC-18/20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	0.2 g
------------	-------

**Technical data customisable plug-in connectors**

Connection cross-section	AWG 18 - AWG 20	Connection cross-section, max.	0.823 mm <sup>2</sup>
Connection cross-section, min.	0.518 mm <sup>2</sup>	Contact material	Cu-alloy
Contact surface	Gold-plated	Number of poles	4
Pollution severity	3	Rated current	7 A

**General Info**

Number of poles	4	Connection 1	M12 Contact
Connection 2	Crimp	Contact material	Cu-alloy
Contact surface	Gold-plated		

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-02-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**SAI-M12-KSC-18/20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****...for M12**

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

**General ordering data**

Type	SAI-TMCSK	Version
Order No.	<a href="#">1381690000</a>	Pressing tool
GTIN (EAN)	4050118183870	
Qty.	1 pc(s).	
Type	SAI-TMC-PD	Version
Order No.	<a href="#">1381700000</a>	Pressing tool
GTIN (EAN)	4050118183856	
Qty.	1 pc(s).	