


ZP 2.5/1AN/5 OR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

Version	Z-series, Plug-in connector, Direct mounting
Order No.	2702430000
Type	ZP 2.5/1AN/5 OR
GTIN (EAN)	4050118711400
Qty.	25 pc(s).

ZP 2.5/1AN/5 OR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	41 mm	Depth (inches)	1.614 inch
Width	25.5 mm	Width (inches)	1.004 inch
Net weight	16.12 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	UL 94 flammability rating	V-0
----------	-------	---------------------------	-----

System specifications

Number of levels	1	Number of clamping points per level	1
Levels cross-connected internally	No		

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Conductors for clamping (rated connection)

Stripping length	10 mm		
------------------	-------	--	--

General

Installation advice	Direct mounting	Standards	In accordance with IEC 60947-7-1
---------------------	-----------------	-----------	----------------------------------

Rating data

Rated cross-section	2.5 mm ²	Standards	In accordance with IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Power loss in accordance with IEC 60947-7-x	0.77 W

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Downloads

Approval/Certificate/Document of Conformity

[Confirmation of Standards EN 45545-2_2020-10](#)

Catalogues

[Catalogues in PDF-format](#)