

**IE-C5DE4UP0200PSSXXX-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Dragline cable, M8 P-code - IP67 straight socket, Open, Cat. 5e, PUR, 20 m
Order No.	<a href="#">2717740200</a>
Type	IE-C5DE4UP0200PSSXXX-E
GTIN (EAN)	4050118778854
Qty.	1 pc(s).

## IE-C5DE4UP0200PSSXXX-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	20 m	Length (inches)	787.402 inch
Net weight	1,232 g		

## Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

## Technical specifications for cable

Bending cycles	2 Mio	Colour coding	white, yellow, blue, orange
Halogen	halogen-free, according to IEC 60754	Insulation	Polyolefin
Number of poles	4	Number of wires	4
Resistance to oils	in accordance with IEC 60811:404	Resistance to spread of flame	Yes
Sheath material	PUR	Sheathing colour	black
Temperature range, moving	-30...70 °C	Temperature range, stationary	-40...80 °C
Test voltage: wire-wire-shield	1 kV DC, 1 min, 1000 V <sub>eff</sub> , 50 Hz, 1 min		

## General technical data

Protection degree	IP67
-------------------	------

## Plug, left

Plug left	M8, P-coded, IP67, female contact, straight, plug, Plastic, shielded
-----------	--

## Plug, right

Plug right	free conductor end
------------	--------------------

## Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**IE-C5DE4UP0200PSSXXX-E**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Wiring

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4