

**IE-C5DE4UP0075PCAPCA-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Dragline cable, M8 P-code - IP67 angeled pin, M8 P-code - IP67 angeled pin, Cat. 5e, PUR, 7.5 m
Order No.	<a href="#">2717800075</a>
Type	IE-C5DE4UP0075PCAPCA-E
GTIN (EAN)	4050118780482
Qty.	1 pc(s).

**IE-C5DE4UP0075PCAPCA-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	7.5 m	Length (inches)	295.276 inch
Net weight	472 g		

**Temperatures**

Operating temperature	-40 °C...80 °C
-----------------------	----------------

**Technical specifications for cable**

Bending cycles	2 Mio	Colour coding	white, yellow, blue, orange
Halogen	halogen-free, according to IEC 60754	Insulation	Polyolefin
Number of poles	4	Number of wires	4
Resistance to oils	in accordance with IEC 60811:404	Resistance to spread of flame	Yes
Sheath material	PUR	Sheathing colour	black
Temperature range, moving	-30...70 °C	Temperature range, stationary	-40...80 °C
Test voltage: wire-wire-shield	1 kV DC, 1 min, 1000 V <sub>eff</sub> , 50 Hz, 1 min		

**General technical data**

Protection degree	IP67
-------------------	------

**Plug, left**

Plug left	M8, P-coded, IP67, male contact, angled 90°, plug, Plastic, shielded
-----------	--

**Plug, right**

Plug right	M8, P-coded, IP67, male contact, angled 90°, plug, Plastic, shielded
------------	--

**Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

Creation date June 7, 2024 5:20:17 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

### IE-C5DE4UP0075PCAPCA-E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Wiring

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4