


SFM 1/24 1.2-1.8 MM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With the comprehensive MultiMark product family, you can achieve optimally structured and sustainable marking in every control cabinet. An example of this is our new SlimFix wire marker, which can be printed and snapped on particularly quickly. At the same time, they meet the highest requirements for vibration and shock resistance. The wire markers have an open design and can be easily and quickly installed before or after the wiring process.

General ordering data

Version	Conductor and cable markers, 1.2 - 1.8 mm, 24 x 3.8 mm, yellow
Order No.	2719080000
Type	SFM 1/24 1.2-1.8 MM GE
GTIN (EAN)	4050118888119
Qty.	700 pc(s).

SFM 1/24 1.2-1.8 MM GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	24 mm	Height (inches)	0.945 inch
Width	3.8 mm	Width (inches)	0.15 inch
Net weight	0.417 g		

General data

Colour	yellow	Halogen	No
Material	PC-ABS, TPU	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Size of labelling field	2.8 x 21.5 mm
Type of printing	neutral	UL 94 flammability rating	V-2
Width	3.8 mm		

Conductor and cable markers

Conductor O.D.	1.2 - 1.8 mm	Conductor O.D., max.	1.8 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.75 mm ²
Conductor cross-section, min.	0.25 mm ²	Cross-section for connected wire	0.25 - 0.75 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

SFM 1/24 1.2-1.8 MM GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



SFM 1/24 1.2-1.8 MM GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	THM MMP ROLLER SFM 1
Order No.	2799000000
GTIN (EAN)	4064675259985
Qty.	1 pc(s).