


**SFM 3/24 2.5-3.3 MM GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

With the comprehensive MultiMark product family, you can achieve optimally structured and sustainable marking in every control cabinet. An example of this is our new SlimFix wire marker, which can be printed and snapped on particularly quickly. At the same time, they meet the highest requirements for vibration and shock resistance. The wire markers have an open design and can be easily and quickly installed before or after the wiring process.

**General ordering data**

Version	SlimFix, Conductor and cable markers, 2.5 - 3.3 mm, 24 x 5.4 mm, yellow
Order No.	<a href="#">2719200000</a>
Type	SFM 3/24 2.5-3.3 MM GE
GTIN (EAN)	4050118888232
Qty.	700 pc(s).
compatible printer	<a href="#">2599430000</a>

**SFM 3/24 2.5-3.3 MM GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	24 mm	Height (inches)	0.945 inch
Width	5.4 mm	Width (inches)	0.213 inch
Net weight	0.3 g		

**General data**

Colour	yellow	Halogen	No
Material	PC-ABS, TPU	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	Orientation of print	horizontal and vertical
Printed characters	without	Size of labelling field	3.7 x 21.5 mm
Type of printing	neutral	UL 94 flammability rating	V-2
Version	with snap-in foot	Width	5.4 mm

**Conductor and cable markers**

Conductor O.D.	2.5 - 3.3 mm	Conductor O.D., max.	3.3 mm
Conductor O.D., min.	2.5 mm	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Cross-section for connected wire	1.5 - 2.5 mm <sup>2</sup>
Halogen	No		

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### SFM 3/24 2.5-3.3 MM GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

