

**DEK 5/8 PLUS FW 1-50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

image/tif

The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, white
Order No.	<a href="#">2748080000</a>
Type	DEK 5/8 PLUS FW 1-50
GTIN (EAN)	4050118891577
Qty.	800 pc(s).

**DEK 5/8 PLUS FW 1-50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Height	5 mm	Height (inches)	0.197 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	0.08 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Application/manufacture	Weidmueller		
Colour	white		
Colour of printing	black		
Halogen	No		
Material	Polyamide 66		
Number of markers per combination	1 MultiCard = Terminal marker		
Number of markers per packaging unit	Form of supply	MultiCard	
Operating temperature range	-40...100 °C		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Orientation of print	horizontal		
Printed characters	Numbers		
UL 94 flammability rating	V-2		
Width	8 mm		

**Connector markers**

Pitch in mm (P)	8 mm
-----------------	------

**Classifications**

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ETIM 9.0	EC000761
ECLASS 9.0	27-14-11-37	ECLASS 9.1	27-14-11-37
ECLASS 10.0	27-14-11-37	ECLASS 11.0	27-28-11-01
ECLASS 12.0	27-28-11-01	ECLASS 13.0	27-28-11-01
ECLASS 14.0	27-28-11-01		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Product Change Notification	<a href="#">Technical change to Dekafix 8 - EN</a> <a href="#">Technical change to Dekafix 8 - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### DEK 5/8 PLUS FW 1-50

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



### Drawing

