

KCMA-42-1000-1A-2.5VA-0.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image, Similar to illustration**

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 1000 A, Secondary current max.: 1 A, Load: 2.5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	2753220000
Type	KCMA-42-1000-1A-2.5VA-0.5
GTIN (EAN)	4050118896701
Qty.	1 pc(s).
Manufacturer	MBS AG

Creation date November 7, 2024 9:51:18 AM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

KCMA-42-1000-1A-2.5VA-0.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	69 mm	Depth (inches)	2.717 inch
Height	96 mm	Height (inches)	3.78 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	606 g		

Temperatures

Operating temperature	-5 °C...50 °C
-----------------------	---------------

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	42 mm
Installation location	Indoor use		

Electrical attributes

Load	2.5 VA	Primary current	1,000 A
Secondary current	0...1 A	Tolerance class	0,5

Technical properties

Cable length	0.5 m	Protection degree	IP20
--------------	-------	-------------------	------

Insulation coordination

Tolerance class	0,5
-----------------	-----

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02
ECLASS 14.0	27-21-09-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
User Documentation	Instruction sheet German
Catalogues	Catalogues in PDF-format

KCMA-42-1000-1A-2.5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

