

HSS-HF 3.2-6.4 EL W75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	TwinMark, Conductor and cable markers, 3.2 - 6.4 mm, white
Order No.	2788640000
Type	HSS-HF 3.2-6.4 EL W75M
GTIN (EAN)	406467506665 1
Qty.	1 pc(s).

HSS-HF 3.2-6.4 EL W75M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.03 inch
Width	10.7 mm	Width (inches)	0.421 inch
Length	75,000 mm	Length (inches)	2,952.75 inch
Net weight	1,060 g		

General data

Colour	white
Halogen	No
Length	75,000 mm
Material	Polyolefine
Number of markers per combination	1 Shrink sleeve reel = Conductor and cable markers
Number of markers per packaging unit	Form of supply Shrink sleeve reel
Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C
Printed characters	without
Type of printing	neutral
Width	10.7 mm

Conductor and cable markers

Conductor O.D.	3.2 - 6.4 mm	Conductor O.D., max.	6.4 mm
Conductor O.D., min.	3.2 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	1.5 mm ²	Cross-section for connected wire	1.5 - 6 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02
ECLASS 14.0	27-28-11-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

HSS-HF 3.2-6.4 EL W75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version
Order No.	2448880000	Ink ribbon
GTIN (EAN)	4050118462944	
Qty.	1 pc(s).	