

**APG 80****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Version	6mm <sup>2</sup> , 400mm <sup>2</sup>
Order No.	<a href="#">2853270000</a>
Type	APG 80
GTIN (EAN)	4064675477020
Qty.	1 pc(s).

**APG 80****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	75 mm	Depth (inches)	2.953 inch
Height	330 mm	Height (inches)	12.992 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	8,360 g		

**Technical data**

Operating voltage	18 V		
Pressing force	nominal	80 kN	

**Description of contact**

Crimping range, max.	400 mm <sup>2</sup>	Crimping range, min.	6 mm <sup>2</sup>
----------------------	---------------------	----------------------	-------------------

**tool data crimping**

Deviation	37 mm	Drive	Battery-operated hydraulic sytem
-----------	-------	-------	----------------------------------

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ETIM 9.0	EC000168
ECLASS 9.0	21-04-38-11	ECLASS 9.1	36-63-06-90
ECLASS 10.0	21-04-38-11	ECLASS 11.0	21-04-38-11
ECLASS 12.0	21-04-38-11	ECLASS 13.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Manual APG 80 multiple language</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## APG 80

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

**General ordering data**

Type	AKKU APG/EPG 2AH
Order No.	<a href="#">2858730000</a>
GTIN (EAN)	4064675566137
Qty.	1 pc(s).

Type	LADEGERAET EPG
Order No.	<a href="#">1509370000</a>
GTIN (EAN)	4050118318630
Qty.	1 pc(s).

Type	AKKU APG/EPG 5AH
Order No.	<a href="#">2860070000</a>
GTIN (EAN)	4064675574750
Qty.	1 pc(s).

**... for tubular cable lugs (acc. to EN 13600)****Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Type	ES APG 80 WM 150	Version
Order No.	<a href="#">1502550000</a>	150mm <sup>2</sup> , WM crimp
GTIN (EAN)	4050118310825	
Qty.	1 pc(s).	

## APG 80

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES APG 80 WM 50	Version
Order No.	<a href="#">1502500000</a>	50mm², WM crimp
GTIN (EAN)	4050118310658	
Qty.	1 pc(s).	
Type	ES APG 80 WM 95	Version
Order No.	<a href="#">1502530000</a>	95mm², WM crimp
GTIN (EAN)	4050118310566	
Qty.	1 pc(s).	
Type	ES APG 80 WM 70	Version
Order No.	<a href="#">1502520000</a>	70mm², WM crimp
GTIN (EAN)	4050118310580	
Qty.	1 pc(s).	
Type	ES APG 80 WM10	Version
Order No.	<a href="#">1502440000</a>	10mm², WM crimp
GTIN (EAN)	4050118310542	
Qty.	1 pc(s).	
Type	ES APG 80 WM 185	Version
Order No.	<a href="#">1502570000</a>	185mm², WM crimp
GTIN (EAN)	4050118310528	
Qty.	1 pc(s).	
Type	ES APG 80 WM 120	Version
Order No.	<a href="#">1502540000</a>	120mm², WM crimp
GTIN (EAN)	4050118310429	
Qty.	1 pc(s).	
Type	ES APG 80 WM 240	Version
Order No.	<a href="#">1502580000</a>	240mm², WM crimp
GTIN (EAN)	4050118310689	
Qty.	1 pc(s).	
Type	ES APG80 WM 400	Version
Order No.	<a href="#">2578060000</a>	400mm², WM crimp
GTIN (EAN)	4064675018124	
Qty.	1 pc(s).	
Type	ES APG 80 WM 16	Version
Order No.	<a href="#">1502470000</a>	16mm², WM crimp
GTIN (EAN)	4050118310498	
Qty.	1 pc(s).	
Type	ES APG 80 WM 35	Version
Order No.	<a href="#">1502490000</a>	35mm², WM crimp
GTIN (EAN)	4050118310597	
Qty.	1 pc(s).	
Type	ES APG 80 WM 300	Version
Order No.	<a href="#">1502590000</a>	300mm², WM crimp
GTIN (EAN)	4050118310511	
Qty.	1 pc(s).	
Type	ES APG 80 WM 25	Version
Order No.	<a href="#">1502480000</a>	25mm², WM crimp
GTIN (EAN)	4050118310634	
Qty.	1 pc(s).	
Type	ES APG 80 WM 6	Version
Order No.	<a href="#">1502430000</a>	6mm², WM crimp
GTIN (EAN)	4050118310801	
Qty.	1 pc(s).	

Creation date July 3, 2024 10:37:07 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

## APG 80

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## ... for compression cable lugs (acc. to DIN 46235)

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Type	ES APG 80 HEX 70	Version
Order No.	<a href="#">1502680000</a>	Hexagonal crimp
GTIN (EAN)	4050118310641	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 120	Version
Order No.	<a href="#">1502700000</a>	Hexagonal crimp
GTIN (EAN)	4050118310931	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 95	Version
Order No.	<a href="#">1502690000</a>	Hexagonal crimp
GTIN (EAN)	4050118310610	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 10	Version
Order No.	<a href="#">1502620000</a>	Hexagonal crimp
GTIN (EAN)	4050118310818	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 16	Version
Order No.	<a href="#">1502630000</a>	Hexagonal crimp
GTIN (EAN)	4050118310436	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 6	Version
Order No.	<a href="#">1502600000</a>	Hexagonal crimp
GTIN (EAN)	4050118310672	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 25	Version
Order No.	<a href="#">1502640000</a>	Hexagonal crimp
GTIN (EAN)	4050118310573	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 185	Version
Order No.	<a href="#">1502730000</a>	Hexagonal crimp
GTIN (EAN)	4050118310726	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 240	Version
Order No.	<a href="#">1502740000</a>	Hexagonal crimp
GTIN (EAN)	4050118310481	
Qty.	1 pc(s).	

Creation date July 3, 2024 10:37:07 AM CEST

## APG 80

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES APG 80 HEX 300	Version
Order No.	<a href="#">1502750000</a>	Hexagonal crimp
GTIN (EAN)	4050118310962	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 35	Version
Order No.	<a href="#">1502650000</a>	Hexagonal crimp
GTIN (EAN)	4050118310696	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 150	Version
Order No.	<a href="#">1502720000</a>	Hexagonal crimp
GTIN (EAN)	4050118310900	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 50	Version
Order No.	<a href="#">1502670000</a>	Hexagonal crimp
GTIN (EAN)	4050118310559	
Qty.	1 pc(s).	
Type	ES APG 80 HEX 300AL	Version
Order No.	<a href="#">1502780000</a>	Hexagonal crimp
GTIN (EAN)	4050118310955	
Qty.	1 pc(s).	

## ... for crimp cable lugs (acc. to DIN 46234)

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

## General ordering data

Type	ES APG 80 DIN 95	Version
Order No.	<a href="#">1502900000</a>	95mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310917	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 6	Version
Order No.	<a href="#">1502820000</a>	6mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310665	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 70	Version
Order No.	<a href="#">1502890000</a>	70mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310719	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 10	Version
Order No.	<a href="#">1502830000</a>	10mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310948	
Qty.	1 pc(s).	

Creation date July 3, 2024 10:37:07 AM CEST

## APG 80

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	ES APG 80 DIN 16	Version
Order No.	<a href="#">1502840000</a>	16mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310979	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 25	Version
Order No.	<a href="#">1502850000</a>	25mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310849	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 35	Version
Order No.	<a href="#">1502870000</a>	35mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310474	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 120	Version
Order No.	<a href="#">1502790000</a>	120mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310832	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 185	Version
Order No.	<a href="#">1501800000</a>	185mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310061	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 150	Version
Order No.	<a href="#">1502800000</a>	150mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310924	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 240	Version
Order No.	<a href="#">1501820000</a>	240mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118309874	
Qty.	1 pc(s).	
Type	ES APG 80 DIN 50	Version
Order No.	<a href="#">1502880000</a>	50mm <sup>2</sup> , Indent crimp
GTIN (EAN)	4050118310450	
Qty.	1 pc(s).	

## ... for wire-end ferrules



## Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

## General ordering data

Type	ES APG 80 AEH 120	Version
Order No.	<a href="#">1502090000</a>	120mm <sup>2</sup> , Trapezoidal crimp
GTIN (EAN)	4050118310146	
Qty.	1 pc(s).	

Creation date July 3, 2024 10:37:07 AM CEST

**APG 80****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	ES APG 80 AEH 70	Version
Order No.	<a href="#">1502070000</a>	70mm², Trapezoidal crimp
GTIN (EAN)	4050118310306	
Qty.	1 pc(s).	
Type	ES APG 80 AEH 95	Version
Order No.	<a href="#">1502080000</a>	95mm², Trapezoidal crimp
GTIN (EAN)	4050118310214	
Qty.	1 pc(s).	
Type	ES APG 80 AEH 50	Version
Order No.	<a href="#">1502050000</a>	50mm², Trapezoidal crimp
GTIN (EAN)	4050118310252	
Qty.	1 pc(s).	
Type	ES APG 80 AEH 150	Version
Order No.	<a href="#">1502100000</a>	150mm², Trapezoidal crimp
GTIN (EAN)	4050118310085	
Qty.	1 pc(s).	