

**WAD 12N MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |  |
|------------|--|
| Version    | Group markers, Cover, 33.3 x 12 mm, WDU 16N, white |
| Order No.  | <a href="#">2866660000</a>                         |
| Type       | WAD 12N MC NE WS                                   |
| GTIN (EAN) | 4064675604877                                      |
| Qty.       | 32 pc(s).  |

**WAD 12N MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Height     | 33.3 mm | Height (inches) | 1.311 inch |
| Width      | 12 mm   | Width (inches)  | 0.472 inch |
| Net weight | 1.238 g |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

**General data**

|                                      |                         |           |
|--------------------------------------|-------------------------|-----------|
| Application/manufacture              | WDU 16N                 |           |
| Colour                               | white                   |           |
| Halogen                              | No                      |           |
| Material                             | Polyamide 66            |           |
| Number of markers per combination    | 1 MultiCard = Cover     |           |
| Number of markers per packaging unit | Form of supply          | MultiCard |
| Operating temperature range          | -40...100 °C            |           |
| Operating temperature range, max.    | 100 °C                  |           |
| Operating temperature range, min.    | -40 °C                  |           |
| Orientation of print                 | horizontal and vertical |           |
| Printed characters                   | neutral                 |           |
| UL 94 flammability rating            | V-2                     |           |
| Width                                | 12 mm                   |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000761    | ETIM 7.0    | EC000761    |
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ECLASS 9.0  | 27-14-11-37 | ECLASS 9.1  | 27-14-11-37 |
| ECLASS 10.0 | 27-14-11-37 | ECLASS 11.0 | 27-28-11-01 |
| ECLASS 12.0 | 27-28-11-01 | ECLASS 13.0 | 27-28-11-01 |

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

**WAD 12N MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**Drawing**