

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Tools, Accessories
Order No.	2903530000
Type	P BAG XL SET 12
GTIN (EAN)	4099986009301
Qty.	1 pc(s).

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	220 mm	Depth (inches)	8.661 inch
Height	60 mm	Height (inches)	2.362 inch
Width	320 mm	Width (inches)	12.598 inch
Net weight	1,847.31 g		

Technical data

Description of article	Toolbag, fitted
------------------------	-----------------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-10-01-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028
RoHS Compliance Status	Compliant

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****VDE-insulated combination pliers**

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	KBZ 180	Version
Order No.	9046290000	Pliers
GTIN (EAN)	4032248356485	
Qty.	1 pc(s).	

Tools

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX ULTIMATE	Version
Order No.	1468880000	Tools, Stripping and cutting tool
GTIN (EAN)	4050118274158	
Qty.	1 pc(s).	

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Slotted screwdriver**

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SLIM 0.6X3.5X100	Version
Order No.	2749610000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896350	thickness (A): 0.6 mm
Qty.	1 pc(s).	
Type	SDIS SLIM 0.8X4.0X100	Version
Order No.	2749620000	Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896367	thickness (A): 0.8 mm
Qty.	1 pc(s).	

Cutting tools

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Type	KT 8	Version
Order No.	9002650000	Cutting tools, Cutting tool for one-hand operation
GTIN (EAN)	4008190020163	
Qty.	1 pc(s).	

P BAG XL SET 12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

VDE insulated telephone pliers



When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	FRZ S 160	Version
Order No.	9046370000	Pliers
GTIN (EAN)	4032248357673	
Qty.	1 pc(s).	

Crosshead screwdriver, Phillips



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIK SLIM PH2 X 100	Version
Order No.	2749660000	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
GTIN (EAN)	4050118896404	
Qty.	1 pc(s).	
Type	SDIK SLIM PH1 X 80	Version
Order No.	2749650000	Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1
GTIN (EAN)	4050118896398	
Qty.	1 pc(s).	

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Voltage tester**

Test instruments are indispensable when installing, servicing and repairing electrical systems and equipment. Weidmüller has a full range of test devices, including voltage testers, clamp-on meters and power socket/circuit-breaker testers. Weidmüller always takes into account the wishes and experience of users in its development and design work, which means that Weidmüller devices are tailored to the needs of practical applications and are extremely reliable.

General ordering data

Type	SD ELEC PRO	Version
Order No.	2855000000	Non-contact voltage tester, No
GTIN (EAN)	4064675530343	
Qty.	1 pc(s).	

Pressing tool

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose. Weidmüller offers a complete line of pliers which comply with national and international testing standards. All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Type	WPZ 250	Version
Order No.	2886220000	Water Pump Pliers
GTIN (EAN)	4064675855224	
Qty.	1 pc(s).	

P BAG XL SET 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****unfitted**

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Type	P BAG BIG	Version
Order No.	2576620000	Tools, Accessories
GTIN (EAN)	4050118650594	
Qty.	1 pc(s).	