

V-ZPA TERMINAL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	
Order No.	2904470000
Type	V-ZPA TERMINAL
GTIN (EAN)	4099986010352
Qty.	1 pc(s).

V-ZPA TERMINAL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	54.3 mm	Depth (inches)	2.138 inch
Height	220.4 mm	Height (inches)	8.677 inch
Width	12.5 mm	Width (inches)	0.492 inch
Net weight	160 g		

Temperatures

Operating temperature	-25 °C...55 °C
-----------------------	----------------

General data

Colour	grey	Design	Adapter plug
Operating altitude	≤ 2000 m	Protection degree	IP20 in installed state
Rail	Busbar		

Insulation coordination acc. to EN 50178

Pollution severity	3
--------------------	---

Rated data IEC / EN

Fuse	NH00, 100 A gG	Number of poles	5
Operating current, I_{max}	125 A	Rated current I_N	101 A
Rated voltage (AC)	240 V	Signalling contact	No
Voltage type	AC		

Connection data

Stripping length	18 mm	Wire connection method	Tension-clamp connection
Wire cross-section, solid, min.	1.5 mm ²	Wire cross-section, solid, max.	25 mm ²
Wire connection cross section, finely stranded, min.	1.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	1.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	16 mm ²

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

V-ZPA TERMINAL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EU Konformitätserklärung / EU Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)