

**V-ZPA FUSE HOLDER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	
Order No.	<a href="#">2904480000</a>
Type	V-ZPA FUSE HOLDER
GTIN (EAN)	4099986010383
Qty.	1 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2024-07-23

## V-ZPA FUSE HOLDER

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	65.5 mm	Depth (inches)	2.579 inch
Height	95.2 mm	Height (inches)	3.748 inch
Width	18.5 mm	Width (inches)	0.728 inch
Net weight	144 g		

## Temperatures

Operating temperature	-25 °C...55 °C	Humidity	5 - 95% rel. humidity
-----------------------	----------------	----------	-----------------------

## General data

Acoustic signal	No	Colour	grey
Design	Adapter plug	Operating altitude	≤ 4000 m
Optical function display	No	Protection degree	IP00
Rail	Busbar		

## Insulation coordination acc. to EN 50178

Pollution severity	2
--------------------	---

## Rated data IEC / EN

Acoustic signal	No	Fuse	6.3 A
Rated current $I_N$	6.3 A	Rated voltage (AC)	240 V
Short-circuit current rating $I_{SCCR}$	25 kA	Signalling contact	No
Standards	IEC 61984	Voltage type	AC

## Connection data

Stripping length	13 mm	Wire connection method	PUSH IN
Clamping range, rated connection	2.5 mm <sup>2</sup>	Wire cross-section, solid, max.	2.5 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	2.5 mm <sup>2</sup>	Connection cross-section, stranded, min.	0.82 mm <sup>2</sup>
Connection cross-section, stranded, max.	2.5 mm <sup>2</sup>		

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

ROHS	Conform
------	---------

### V-ZPA FUSE HOLDER

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity

[EU\\_Konformitätserklärung / EU\\_Declaration\\_of\\_Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Beipackzettel / Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

## V-ZPA FUSE HOLDER

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

