

RC M P3 M20 C SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

AC connector:

These circular connectors enable a quick connection with a high protection class. They are available both as plugs and sockets.

General ordering data

Order No.	2992980000
Type	RC M P3 M20 C SP
GTIN (EAN)	4099986872059

RC M P3 M20 C SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.015 g
------------	---------

Temperatures

Operating temperature	-40 °C...60 °C
-----------------------	----------------

Technical data customisable plug-in connectors

Cable diameter, max.	13 mm	Cable diameter, min.	7 mm
Coding	none	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Connection cross-section, max.	4 mm ²
Connection cross-section, min.	0.5 mm ²	Contact material	Brass
Contact surface	Brass	Housing main material	PA 66
Number of poles	3	Protection degree	IP68
Rated current	17.5 A	Rated voltage	500 V
Shield connection	No	Type of connection	PUSH IN

General data

Housing main material	PA 66	Number of poles	3
Type of connection	PUSH IN		

Technical data

Cable diameter, max.	13 mm	Cable diameter, min.	7 mm
Coding	none	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Contact material	Brass
Contact surface	Brass	Protection degree	IP68
Rated current	17.5 A	Rated impulse withstand voltage	2.5 kV
Rated voltage	500 V	Shield connection	No
Stripping length	6 mm	UL 94 flammability rating	V-0

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

RC M P3 M20 C SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



RC M P3 M20 C SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****AC connectors**

AC connector:

These circular connectors enable a quick connection with a high protection class. They are available both as plugs and sockets.

General ordering data

Type	RC F P3 C SP
Order No.	2992970000
GTIN (EAN)	4099986872042
Qty.	

Round connector M20 mounting tool

Tool:

This tool is ideal for installing the M20 built-in connectors.

General ordering data

Type	MTA RC
Order No.	2884950000
GTIN (EAN)	4064675852070
Qty.	