

**TS35X15 ST K71****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

The system accessories for the Klippon® K enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35 and TS15
- Mounting plates
- Hinges
- Wall-mounted holder

**General ordering data**

|            |   |
|------------|---|
| Version    | Rail, TS 35, TS 35 x 15, Width: 260 mm, with slot, Steel, galvanic zinc plated and passivated |
| Order No.  | <a href="#">8000073099</a>  |
| Type       | TS35X15 ST K71  |
| GTIN (EAN) | 4064675340539   |
| Qty.       | 20 pc(s).   |

**TS35X15 ST K71****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 15 mm  | Depth (inches)  | 0.591 inch  |
| Height     | 35 mm  | Height (inches) | 1.378 inch  |
| Width      | 260 mm | Width (inches)  | 10.236 inch |
| Net weight | 180 g  |                 |             |

**General information**

|                     |                                     |           |              |
|---------------------|-------------------------------------|-----------|--------------|
| Installation advice | Direct mounting                     | Material  | Steel        |
| Material thickness  | 1.5 mm                              | Standards | DIN EN 60715 |
| Surface finish      | galvanic zinc plated and passivated |           |              |

**General information on accessories**

|                |                                     |                    |        |
|----------------|-------------------------------------|--------------------|--------|
| Material       | Steel                               | Material thickness | 1.5 mm |
| Surface finish | galvanic zinc plated and passivated |                    |        |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001285    | ETIM 7.0    | EC001285    |
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ECLASS 9.0  | 27-40-06-02 | ECLASS 9.1  | 27-40-06-02 |
| ECLASS 10.0 | 27-40-06-02 | ECLASS 11.0 | 27-40-06-02 |
| ECLASS 12.0 | 27-40-06-02 | ECLASS 13.0 | 27-40-06-02 |

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |