

**TS35X15 ST KTB2215 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

**General ordering data**

Version	Rail, TS 35, TS 35 x 15, Width: 174 mm, without slot, Steel, galvanic zinc plated and passivated
Order No.	<a href="#">8000073109</a>
Type	TS35X15 ST KTB2215 VER
GTIN (EAN)	4064675340591
Qty.	20 pc(s).

**TS35X15 ST KTB2215 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	174 mm	Width (inches)	6.85 inch
Net weight	120 g		

**General information**

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1.5 mm
Standards	DIN EN 60715	Surface finish	galvanic zinc plated and passivated

**General information on accessories**

Material	Steel	Material thickness	1.5 mm
Surface finish	galvanic zinc plated and passivated		

**Classifications**

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

**Environmental Product Compliance**

REACH SVHC /

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**TS35X15 ST KTB2215 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Mounting plates**

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

**General ordering data**

Type	GFSC M5X10 TX20 SET	Version
Order No.	<a href="#">1274150000</a>	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Material: Steel, galvanized, galvanic zinc
Qty.	1 pc(s).	plated and passivated, silver