

**TS35X7.5 ST KTB5040 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

**General ordering data**

|            |  |
|------------|--|
| Version    | Klippon TB (Terminal Box), Enclosures, without slot, Height: 35 mm, Width: 453 mm, Depth: 7.5 mm, Material: Steel, galvanic zinc plated and passivated, silver |
| Order No.  | <a href="#">8000116102</a>   |
| Type       | TS35X7.5 ST KTB5040 VER  |
| GTIN (EAN) | 4099986820487  |
| Qty.       | 20 pc(s).  |

Creation date May 23, 2024 1:40:14 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

**TS35X7.5 ST KTB5040 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 7.5 mm   | Depth (inches)  | 0.295 inch  |
| Height     | 35 mm    | Height (inches) | 1.378 inch  |
| Width      | 453 mm   | Width (inches)  | 17.835 inch |
| Net weight | 93.863 g |                 |             |

**General information**

|                     |                                     |                 |              |
|---------------------|-------------------------------------|-----------------|--------------|
| Installation advice | Direct mounting                     | Integral fixing | Screwed      |
| Material            | Steel                               | Standards       | DIN EN 60715 |
| Surface finish      | galvanic zinc plated and passivated |                 |              |

**General information on accessories**

|          |       |                |                                     |
|----------|-------|----------------|-------------------------------------|
| Material | Steel | Surface finish | galvanic zinc plated and passivated |
|----------|-------|----------------|-------------------------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001285    | ETIM 7.0    | EC001285    |
| ETIM 8.0    | EC001285    | ETIM 9.0    | EC001285    |
| ECLASS 9.0  | 27-40-06-02 | ECLASS 9.1  | 27-40-06-02 |
| ECLASS 10.0 | 27-40-06-02 | ECLASS 11.0 | 27-40-06-02 |
| ECLASS 12.0 | 27-40-06-02 | ECLASS 13.0 | 27-40-06-02 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**TS35X7.5 ST KTB5040 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Mounting plates**

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

**General ordering data**

| Type       | GFSC M5X10 TX20 SET        | Version   |
|------------|----------------------------|---|
| Order No.  | <a href="#">1274150000</a> | Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width: |
| GTIN (EAN) | 4050118063820              | 8.5 mm, Depth: 8.5 mm, Material: Steel, galvanized, galvanic zinc   |
| Qty.       | 1 pc(s).                   | plated and passivated, silver                                       |