

TS20/CX10 ST ZN 9191 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

General ordering data

Version	Klippon TB (Terminal Box), Enclosures, Height: 20 mm, Width: 860 mm, Depth: 10 mm, Material: Steel, galvanized, silver
Order No.	8000117045
Type	TS20/CX10 ST ZN 9191 VER
GTIN (EAN)	4099986829879
Qty.	20 pc(s).

TS20/CX10 ST ZN 9191 VER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	10 mm	Depth (inches)	0.394 inch
Height	20 mm	Height (inches)	0.787 inch
Width	860 mm	Width (inches)	33.858 inch
Net weight	415.85 g		

General information

Installation advice	Screw	Material	Steel
Surface finish	galvanized		

General information on accessories

Material	Steel	Surface finish	galvanized
----------	-------	----------------	------------

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02
ECLASS 14.0	27-40-06-02		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

TS20/CX10 ST ZN 9191 VER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

Type	GFSC M5X10 TX20 SET	Version
Order No.	1274150000	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Material: Steel, galvanized, galvanic zinc
Qty.	1 pc(s).	plated and passivated, silver