

**IE-C-IP67****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

SnapIn plug-in connectors according to IEC 61076-3-106  
ver.6 in plastic, with RJ45 insert

**General ordering data**

Version	Connecting plug, Cable coupling, IP67, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	<a href="#">8813090000</a>
Type	IE-C-IP67
GTIN (EAN)	4032248512843
Qty.	1 pc(s).

## IE-C-IP67

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	76 g
------------	------

## Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

## General data

Connection 1	RJ45	Connection 2	IDC
Description of article		Configuration	Coupling including RJ 45 module with IDC connection
Wiring	Cable coupling Colour-coded pin assignment according to EIA/TIA T568 A., EIA/TIA T568 B	Colour	Light Grey
Housing main material	PA 66, UL 94: V-0	Category	Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)
Contact surface	Gold over nickel	Sheath diameter, min.	6 mm
Sheath diameter, max.	9.5 mm	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Shielding	360°; shield contact	Protection degree	IP67
Plugging cycles	750		

## General standards

Certificate No. (DNV)	TAE00003EW	Connector standard	IEC 61076-3-106 Var. 6, IEC 60603-7-5
-----------------------	------------	--------------------	---------------------------------------

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

Creation date June 4, 2024 1:04:23 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

### IE-C-IP67

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing

