

**AM 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Sheathing stripper for PVC cables

**General ordering data**

Version	Tools, Sheathing strippers
Order No.	<a href="#">9001540000</a>
Type	AM 25
GTIN (EAN)	4008190138271
Qty.	1 pc(s).

**AM 25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	33 mm	Depth (inches)	1.299 inch
Height	157 mm	Height (inches)	6.181 inch
Width	47 mm	Width (inches)	1.85 inch
Net weight	120.67 g		

**Technical data**

Description of article	Sheathing strippers
------------------------	---------------------

**Stripping tools**

Cable type	PVC round cable	Cut depth	adjustable up to 4.5 mm
Max. conductor diameter	25 mm	Min. conductor diameter	6 mm

**Classifications**

ETIM 6.0	EC000163	ETIM 7.0	EC000163
ETIM 8.0	EC000163	ETIM 9.0	EC000163
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## AM 25

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



### Example of use



**AM 25****Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Accessories / replacement parts**

Sheathing stripper for PVC cables

**General ordering data**

Type	ERSATZMESSER AM 25/35	Version
Order No.	<a href="#">9001530000</a>	Accessories, Spare cutting blade
GTIN (EAN)	4008190154813	
Qty.	2 pc(s).	