

STRIPAX PLUS 2.5 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Cutting, stripping and crimping tools for connected wire-end ferrules strips**

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved
- Only strips of linked wire end ferrules, each containing 50 pieces, from Weidmüller may be processed. The use of wire end ferrules on reels may lead to destruction.

General ordering data

| | |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Version | Cutting, stripping and crimping tool, Crimping tool for wire-end ferrules, 0.5mm ² , 2.5mm ² , Trapezoidal crimp |
| Order No. | 9011980000 |
| Type | STRIPAX PLUS 2.5 ZERT |
| GTIN (EAN) | 4008190004613 |
| Qty. | 1 pc(s). |
| Replacement parts | 9050340000 2917160000 |

STRIPAX PLUS 2.5 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|----------------|------------|
| Width | 210 mm | Width (inches) | 8.268 inch |
| Net weight | 307 g | | |

Technical data

| | |
|------------------------|------------------|
| Description of article | (1)Crimping tool |
|------------------------|------------------|

Description of contact

| | | | |
|-----------------------------------|------------------------------------|-----------------------------------|---------------------|
| Conductor cross-section, max. AWG | AWG 14 | Conductor cross-section, min. AWG | AWG 20 |
| Crimping range, max. | 2.5 mm ² | Crimping range, min. | 0.5 mm ² |
| Type of contact | Strips of linked wire-end ferrules | | |

tool data crimping

| | |
|-----------------------|-------------------|
| Crimping type/profile | Trapezoidal crimp |
|-----------------------|-------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002109 | ETIM 7.0 | EC002109 |
| ETIM 8.0 | EC002109 | ETIM 9.0 | EC002109 |
| ECLASS 9.0 | 21-04-37-06 | ECLASS 9.1 | 21-04-37-06 |
| ECLASS 10.0 | 21-04-37-06 | ECLASS 11.0 | 21-04-37-06 |
| ECLASS 12.0 | 21-04-37-06 | ECLASS 13.0 | 21-04-37-06 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2159813b-98fd-4068-b62a-bc89a046c012 |

Downloads

| | |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Product Change Notification | Technische Änderung für Crimpwerkzeug stripax plus 2.5 Technical change to Crimping tool Stripax plus 2.5 |
| User Documentation | Manual |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

STRIPAX PLUS 2.5 ZERT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Example of use



Example of use




STRIPAX PLUS 2.5 ZERT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Replacement parts****Accessories / replacement parts****Cutting, stripping and crimping tools for connected wire-end ferrules strips**

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved
- Only strips of linked wire end ferrules, each containing 50 pieces, from Weidmüller may be processed. The use of wire end ferrules on reels may lead to destruction.

General ordering data

| | |
|------------|----------------------------|
| Type | ERTE AIME SPX P II |
| Order No. | 2917160000 |
| GTIN (EAN) | 4099986548121 |
| Qty. | 1 pc(s). |

| | | |
|------------|----------------------------|---------------------|
| Type | ERSATZMESSER STRIPAX PL | Version |
| Order No. | 9050340000 | Spare cutting blade |
| GTIN (EAN) | 4008190350949 | |
| Qty. | 5 pc(s). | |

STRIPAX PLUS 2.5 ZERT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| Type | H1,0/14D R BD | Version | Packaging |
|------------|----------------------------|-------------------------------------------------|-----------|
| Order No. | 9004330000 | Wire-end ferrule, Standard, 10 mm, 8 mm, red | Reel |
| GTIN (EAN) | 4008190047498 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H1,0/14 GE BD | Version | Packaging |
| Order No. | 9004320000 | Wire-end ferrule, Standard, 10 mm, 8 mm, yellow | Reel |
| GTIN (EAN) | 4008190167523 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H1,0/14T R BD | Version | Packaging |
| Order No. | 9021950000 | Wire-end ferrule, Standard, 10 mm, 8 mm, red | Reel |
| GTIN (EAN) | 4008190262747 | | packaged |
| Qty. | 500 pc(s). | | |

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

| Type | H1,5/14 R BD | Version | Packaging |
|------------|----------------------------|------------------------------------------------|-----------|
| Order No. | 9004340000 | Wire-end ferrule, Standard, 10 mm, 8 mm, red | Tape |
| GTIN (EAN) | 4008190080723 | | |
| Qty. | 500 pc(s). | | |
| Type | H1,5/14D SW BD | Version | Packaging |
| Order No. | 9004350000 | Wire-end ferrule, Standard, 10 mm, 8 mm, black | Reel |
| GTIN (EAN) | 4008190005474 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H1,5/14T SW BD | Version | Packaging |
| Order No. | 9021960000 | Wire-end ferrule, Standard, 10 mm, 8 mm, black | Reel |
| GTIN (EAN) | 4008190262389 | | packaged |
| Qty. | 500 pc(s). | | |

STRIPAX PLUS 2.5 ZERT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- DIN colour code
- other colour code

General ordering data

| Type | H2,5/14T GR BD | Version | Packaging |
|------------|----------------------------|-----------------------------------------------|-----------|
| Order No. | 9004370000 | Wire-end ferrule, Standard, 11 mm, 8 mm, grey | Reel |
| GTIN (EAN) | 4008190052508 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H2,5/14D BL BD | Version | Packaging |
| Order No. | 9004360000 | Wire-end ferrule, Standard, 10 mm, 8 mm, blue | Reel |
| GTIN (EAN) | 4008190083397 | | packaged |
| Qty. | 500 pc(s). | | |

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| Type | H0,75/14D GR BD | Version | Packaging |
|------------|----------------------------|-----------------------------------------------------|-----------|
| Order No. | 9004300000 | Wire-end ferrule, Standard, 10 mm, 8 mm, grey | Reel |
| GTIN (EAN) | 4008190154837 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H0,75/14T HBL BD | Version | Packaging |
| Order No. | 9004310000 | Wire-end ferrule, Standard, 10 mm, 8 mm, Light Blue | Reel |
| GTIN (EAN) | 4008190179298 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H0,75/14 W BD | Version | Packaging |
| Order No. | 9004290000 | Wire-end ferrule, Standard, 10 mm, 8 mm, white | Reel |
| GTIN (EAN) | 4008190006778 | | packaged |
| Qty. | 500 pc(s). | | |


STRIPAX PLUS 2.5 ZERT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts


Cutting, stripping and crimping tools for connected wire-end ferrules strips

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved
- Only strips of linked wire end ferrules, each containing 50 pieces, from Weidmüller may be processed. The use of wire end ferrules on reels may lead to destruction.

General ordering data

Type ERTE AIME SPX P II
 Order No. [2917160000](#)
 GTIN (EAN) 4099986548121
 Qty. 1 pc(s).

| Type | ERSATZMESSER STRIPAX PL | Version |
|------------|----------------------------|---------------------|
| Order No. | 9050340000 | Spare cutting blade |
| GTIN (EAN) | 4008190350949 | |
| Qty. | 5 pc(s). | |

Strip of wire end ferrules



- Linked of wire-end ferrule strips (50 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

| Type | H0,5/14T W BD | Version | Packaging |
|------------|----------------------------|-------------------------------------------------|-----------|
| Order No. | 9021930000 | Wire-end ferrule, Standard, 10 mm, 8 mm, white | Reel |
| GTIN (EAN) | 4008190262402 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H0,5/14D W BD | Version | Packaging |
| Order No. | 9004280000 | Wire-end ferrule, Standard, 10 mm, 8 mm, white | Reel |
| GTIN (EAN) | 4008190162627 | | packaged |
| Qty. | 500 pc(s). | | |
| Type | H0,5/14 OR BD | Version | Packaging |
| Order No. | 9004270000 | Wire-end ferrule, Standard, 10 mm, 8 mm, orange | Reel |
| GTIN (EAN) | 4008190091774 | | packaged |
| Qty. | 500 pc(s). | | |