

**CRIMP-SET PZ 3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimp sets

**General ordering data**

Version	Assortment crimping tool, Crimping tool: PZ 3, Stripping tool: STRIPAX, Crimping range, min.: 0.5, Colour code: Weidmüller
Order No.	<a href="#">9028650000</a>
Type	CRIMP-SET PZ 3
GTIN (EAN)	4032248384044
Qty.	1 pc(s).
Packaging	Plastic box

Creation date June 4, 2024 11:50:47 PM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**CRIMP-SET PZ 3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	261 mm	Depth (inches)	10.276 inch
Height	57 mm	Height (inches)	2.244 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	1,723.38 g		

**Technical data**

Description of article	Set includes crimping tool for up to 6 mm <sup>2</sup> , stripping tool and wire-end ferrules in Weidmüller colour code
------------------------	---

**Assortments**

Colour code	Weidmüller	Crimping range, max.	6 mm <sup>2</sup>
Crimping range, min.	0.5 mm <sup>2</sup>	Crimping tool	PZ 3
Number of AEH	3,100 pcs.	Packaging	Plastic box
Stripping tool	STRIPAX		

**Classifications**

ETIM 6.0	EC000524	ETIM 7.0	EC000524
ETIM 8.0	EC000524	ETIM 9.0	EC000524
ECLASS 9.0	27-40-02-18	ECLASS 9.1	27-40-02-18
ECLASS 10.0	27-40-02-18	ECLASS 11.0	27-40-02-18
ECLASS 12.0	27-40-02-18	ECLASS 13.0	27-40-02-18

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## CRIMP-SET PZ 3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## packed loose in polythene bag



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

## General ordering data

Type	H1,5/14 R	Version	Packaging
Order No.	<a href="#">0463100000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, red	loose
GTIN (EAN)	4008190065089		
Qty.	500 pc(s).		

## Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

## General ordering data

Type	EINSATZ A8-1 CL55	Version
Order No.	<a href="#">9028460000</a>	Assortment of inserts
GTIN (EAN)	4032248310029	
Qty.	100 pc(s).	
Type	EINSATZ A7-1 CL55	Version
Order No.	<a href="#">9028450000</a>	Assortment of inserts
GTIN (EAN)	4032248310012	
Qty.	1 pc(s).	

## CRIMP-SET PZ 3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Crimping tools

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

## General ordering data

Type	PZ 3	Version
Order No.	<a href="#">0567300000</a>	Pressing tool, Crimping tool for wire-end ferrules, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> ,
GTIN (EAN)	4008190052423	Square crimp
Qty.	1 pc(s).	

## packed loose in polythene bag



- supplied loose in polybag
- DIN colour code
- other colour code

## General ordering data

Type	H2,5/15D BL	Version	Packaging
Order No.	<a href="#">9019160000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, blue	loose
GTIN (EAN)	4008190028732		
Qty.	500 pc(s).		

**CRIMP-SET PZ 3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H1,0/14 GE	Version		Packaging	
Order No.	<a href="#">0463000000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow		loose	
GTIN (EAN)	4008190024697				
Qty.	500 pc(s).				

**Case**

- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

**General ordering data**

Type	KOFFER PSC4-01	Version	
Order No.	<a href="#">9028860000</a>	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 pc(s).		

**CRIMP-SET PZ 3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Type	H0,75/14 W	Version		Packaging	
Order No.	<a href="#">0462900000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, white		loose	
GTIN (EAN)	4008190033248				
Qty.	500 pc(s).				

**packed loose in polythene bag**

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

**General ordering data**

Type	H0,5/14 OR	Version		Packaging	
Order No.	<a href="#">0690700000</a>	Wire-end ferrule, Standard, 10 mm, 8 mm, orange		loose	
GTIN (EAN)	4008190015770				
Qty.	500 pc(s).				

## CRIMP-SET PZ 3

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Conductor nom. cross-section 6.0mm<sup>2</sup>

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

## General ordering data

Type	H6,0/20 SW	Version		Packaging	
Order No.	<a href="#">0533500000</a>	Wire-end ferrule, Standard, 14 mm, 12 mm, black		loose	
GTIN (EAN)	4008190183905				
Qty.	100 pc(s).				

## Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

## General ordering data

Type	STRIPAX	Version	
Order No.	<a href="#">9005000000</a>	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 pc(s).		